

IE-SR-4TX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Weidmüller Industrial Security Routers

- Secure networks
 - Stateful packet inspection Firewall
 - IP/Port- forwarding
 - Network segmentation
- Easy integration of machine networks into manufacturing networks through 1: 1 NAT
- Secure and easy remote maintenance with Weidmüller u-link remote access service
- Enable modular and future proof network architectures with static and dynamic routing
- Secure communication over the Internet by using IPsec and OpenVPN
- Reliable internet connection, even without on-site internet access, thanks to integrated 4G/LTE cellular modem
- Full flexibility thanks to Fast Ethernet and Gigabit Ethernet interfaces ranging from 2 up to 4 ports.

General ordering data

Version	Security/NAT/VPN/U-link Router, Fast Ethernet, 4x RJ45 10/100BaseT(X), IP30, -30 °C...70 °C
Order No.	2751270000
Type	IE-SR-4TX
GTIN (EAN)	4050118899955
Qty.	1 items

IE-SR-4TX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

Dimensions and weights

Depth	94.8 mm	Depth (inches)	3.7323 inch
Height	134.5 mm	Height (inches)	5.2953 inch
Width	29.9 mm	Width (inches)	1.1772 inch
Net weight	175 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-30 °C...70 °C
Humidity	5 - 90 %, no condensation		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption		
RoHS Exemption (if applicable/known)	6c, 7a, 7cI		
REACH SVHC	Lead 7439-92-1		
SCIP	9229992a-00b9-4096-8962-200a7f33e289		

EMC conformity and approvals

EMC standards	EN 55032, EN 55024, EN 61000-6-2, EN 61000-6-4	Vibration	according to IEC 60068-2-6
Shock	according to IEC 60068-2-27	Safety standard	UL 61010-1, UL 61010-2-201

Environmental conditions

Operating temperature, max.	70 °C		
Operating temperature, min.	-30 °C		
Humidity	5 - 90 %, no condensation		
Storage temperature, max.	85 °C		
Storage temperature, min.	-40 °C		
Operating altitude	Altitude, max.	2000 m	
	Note	in acc. with UL	
	Altitude, max.	6000 m	
	Note	for restrictions, see the manufacturer's declaration for operating altitude in section downloads	

Guarantee

Time interval	3 years
---------------	---------

IE-SR-4TX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Interfaces

RJ45 ports	10/100BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port	Number of ports	4x RJ45 10/100BaseT(X)
Function reset button	Restoration of factory settings	Digital inputs	1x, galvanically isolated, VPN-initiate: establishes a pre-configured VPN connection (24 V in), Cut: physically disconnects (Link Down) the WAN port (24 V in), Trigger pre-configured packet filter rules (24 V in)
SCM-Card slot type	Smart Card (ID-000 format), Save and restore the configuration using smart card (memory chip)	Serial port	1x RS-485, 2-wire, galvanically isolated, 1 removable 3-pole terminal block
Number of SCM-Card slots	1	LED indicator	Power: indicates power supply status, boot-up process, firmware update process, Status: indicates system status, VPN: indicates VPN tunnel status, Port LED: Link/ACT, Speed (RJ45 port)

Management features

Device configuration	Webbrowser (HTTP/HTTPS), SNMP v3, Windows tool	Monitoring function	SNMP v3, Syslog, Event based warning via SNMP trap
IP-address management	Static, DHCP-Client, DHCP-Server (pool-based), DNS-Relay	Time synchronization management	NTP client, NTP server
Industrial protocol support	Modbus/TCP slave		

Power supply

Reverse polarity protection	Yes	
Supply voltage	24 V DC, 1 single input	
Overload current protection	Yes	
Connection type	1 removable 4-pin terminal block	
Voltage supply range	Voltage type	DC
	Voltage, min.	19.2 V
	Voltage, max.	28.8 V
Current consumption	Voltage	24 V
	Current	0.8 A

Routing Features

NAT functions	Source / Destination NAT (Port / Host / Network)	Firewall functions	Stateful Packet Inspection Firewall (Layer-3), Transparent bridge mode (4-port switch with additional Layer-2 filter)
VPN functions	u-link client, OpenVPN (Server or Client), IPSec (Initiator or Responder)	Routing functions	IPv4 routing, Static and dynamic IP Routing, RIPv2 / OSPF

IE-SR-4TX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Technical data

Housing main material	Plastic	Type of mounting	DIN rail
Protection degree	IP30	Speed	Fast Ethernet

Technology

Standard	IEEE 802.3 for 10BASE-T, IEEE 802.3u for 100BASE-TX
----------	--

Important note

Product information	For the SCM card usage please check the compatibility list for suitable router models and hardware revisions found at the SCM card IE-EBR-SMARTCARD-SR 2909820000.
---------------------	--

Classifications

ETIM 8.0	EC001478	ETIM 9.0	EC001478
ETIM 10.0	EC001478	ECLASS 14.0	19-17-04-05
ECLASS 15.0	19-17-04-05		

Accessories

u-link Remote Access Service



The Weidmüller u-link remote access service offers an easy possibility to securely access ethernet devices in a remote network.

With the u-link VPN Server as the central meeting point server, the VPN clients (service PC and Weidmüller u-link client devices) always connect outbound and thus conform to the typical IT security requirements. Separate database and server instances are used for each u-link customer account (secure client isolation) to ensure data integrity.

Communication between the u-link VPN server and remote clients (service PCs and u-link client devices) takes place via a certificate-protected openVPN connection. The u-link creed is "configuration instead of programming" the use is intuitive and does not require expert knowledge.

Featureset:

- 1-click VPN remote access for service PC's
- easyAccess: web, rdp or vnc connections to remote hosts fully browser based for use with tablet or smartphone
- Organization and Group Management
- Topologies including 3rd party end-devices
- Firmware management: Display of firmware status of all routers and the option of a time-controlled, automated firmware update
- Individual access rights: granular configuration of access rights to devices in the target network
- Extensive event log: Presentation of all activities in the u-link portal with extensive filter and export functions
- Password policy: Increased security through configurable specification of minimum requirements for password quality and validity period

Weidmüller offers the following usage variations and additional options for the u-link Remote Access Service:

Basic version:

- Automatically assigned by registering at u-link.weidmueller.com
- Free use for 6 months, extended to 365 days when registering a new u-link client device
- Full featureset
- Unlimited users
- Max. 50 u-link capable devices (access points to a remote network)
- 1 simultaneous VPN connection
- No data or speed limitations (subject to normal market usage)

Extensions

- Additional 50/100/250/500/1000 or more u-link capable devices
- Additional simultaneous VPN connections
- China-VPN: secure and reliable VPN connection to and from China

IE-SR-4TX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

General ordering data

Type	U-LINK-BASIC-EXTENSION...	Version
Order No.	3024610000	License code for u-link Remote Access Service., Extends the period of
GTIN (EAN)		the basic license by 1 year.
Qty.	1 ST	
Type	U-LINK-50-DEVICES-1Y	Version
Order No.	2870090000	License code for u-link Remote Access Service., Adds 50 additional
GTIN (EAN)		configurable u-link clients on Weidmüller hardware to the basic
Qty.	1 ST	license and extends the period of the basic license accordingly.
Type	U-LINK-100-DEVICES-1Y	Version
Order No.	2870100000	License code for u-link Remote Access Service., Adds 100 additional
GTIN (EAN)		configurable u-link clients on Weidmüller hardware to the basic
Qty.	1 ST	license and extends the period of the basic license accordingly.
Type	U-LINK-250-DEVICES-1Y	Version
Order No.	2870110000	License code for u-link Remote Access Service., Adds 250 additional
GTIN (EAN)		configurable u-link clients on Weidmüller hardware to the basic
Qty.	1 ST	license and extends the period of the basic license accordingly.
Type	U-LINK-500-DEVICES-1Y	Version
Order No.	2870120000	License code for u-link Remote Access Service., Adds 500 additional
GTIN (EAN)		configurable u-link clients on Weidmüller hardware to the basic
Qty.	1 ST	license and extends the period of the basic license accordingly.
Type	U-LINK-1000-DEVICES-1Y	Version
Order No.	2924220000	License code for u-link Remote Access Service., Adds 1000 additional
GTIN (EAN)		configurable u-link clients on Weidmüller hardware to the basic
Qty.	1 ST	license and extends the period of the basic license accordingly.
Type	U-LINK-1-CONNECTION-1Y	Version
Order No.	2870130000	"VPN connection" licence code for u-link Remote Access Service. Can
GTIN (EAN)		be used as an additional VPN connection or to extend the period of a
Qty.	1 ST	VPN connection that has already been activated
Type	U-LINK-CNSERVER-1Y	Version
Order No.	2870140000	License code for u-link Remote Access Service., Allows the use of the
GTIN (EAN)		server in China for a secure and reliable VPN connection to and from
Qty.	1 ST	China.

Mounting kit for 19" rack assembly

- For assembling DIN rail-based devices on 19" racks



General ordering data

Type	RM-KIT	Version
Order No.	1241440000	Kit for 19"-rack mounting
GTIN (EAN)	4050118029154	
Qty.	1 ST	

IE-SR-4TX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

Accessories

www.weidmueller.com

Ethernet



- Suitable for Cat. 5 (up to 100 MHz) and Cat. 6 (up to 250 MHz Class E)
- Suitable for PoE+ (according to IEEE 802.3at, IEEE 802.3bt Type 3 and 4)
- Protection of all wire pairs
- Connection via RJ45 sockets
- Metal housing

General ordering data

Type	VDATA CAT6	Version	
Order No.	1348590000	Terminal rail fixing, Surge protection, Cat.6, PoE, 802.3 bt at Type 1,	
GTIN (EAN)	4050118153002	802.3 bt at Type 2, 802.3 bt at Type 3, 802.3 bt at Type 4	
Qty.	1 ST		

Industrial Security Router



Weidmüller Industrial Security Routers

- Secure networks
 - Stateful packet inspection Firewall
 - IP/Port- forwarding
 - Network segmentation
- Easy integration of machine networks into manufacturing networks through 1: 1 NAT
- Secure and easy remote maintenance with Weidmüller u-link remote access service
- Enable modular and future proof network architectures with static and dynamic routing
- Secure communication over the Internet by using IPsec and OpenVPN
- Reliable internet connection, even without on-site internet access, thanks to integrated 4G/LTE cellular modem
- Full flexibility thanks to Fast Ethernet and Gigabit Ethernet interfaces ranging from 2 up to 4 ports.

General ordering data

Type	IE-EBR-SMARTCARD-SR	Version	
Order No.	2909820000	Router smartcard,	
GTIN (EAN)	4099986227361		
Qty.	1 ST		