

KCMA-18-125-1A-1,5VA-3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image, Similar to illustration

Current transformers for retrofitting

Features:

- especially suitable for use in hard-to-reach places
- no cutting of the primary conductors necessary
- Unfolding of the current transformer without additional tools

General ordering data

Version	Primary current: 125 A, Secondary current max.: 1 A, Load: 1.5 VA, Tolerance class: 3, Split-core current transformer
Order No.	2752980000
Type	KCMA-18-125-1A-1,5VA-3
GTIN (EAN)	4050118897005
Qty.	1 items
Manufacturer	MBS AG

KCMA-18-125-1A-1,5VA-3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	67.3 mm	Depth (inches)	2.6496 inch
Height	64.5 mm	Height (inches)	2.5394 inch
Width	41.6 mm	Width (inches)	1.6378 inch
Net weight	260.48 g		

Temperatures

Storage temperature Operating temperature -5 °C...50 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Dimensions of live conductors

Type of conductor Insulated conductor only Round conductor 18.50 mm
 Installation location Indoor use

Electrical attributes

Tolerance class 3 Secondary current 0...1 A
 Load 1.5 VA Primary current 125 A

Technical properties

Cable length 2.5 m Protection degree IP20
 Nominal frequency 50 Hz

Insulation coordination

Tolerance class 3

Classifications

ETIM 8.0	EC002048	ETIM 9.0	EC002048
ETIM 10.0	EC002048	ECLASS 14.0	27-21-09-02
ECLASS 15.0	27-21-09-02		

