

KCMA-18-100-1A-0.3VA-1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image, Similar to illustration



Current transformers for retrofitting

Features:

- especially suitable for use in hard-to-reach places
- no cutting of the primary conductors necessary
- Unfolding of the current transformer without additional tools

General ordering data

Version	Primary current: 100 A, Secondary current max.: 1 A, Load: 0.3 VA, Tolerance class: 1, Split-core current transformer
Order No.	2752990000
Type	KCMA-18-100-1A-0.3VA-1
GTIN (EAN)	4050118896794
Qty.	1 items
Manufacturer	MBS AG

KCMA-18-100-1A-0.3VA-1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	59 mm	Depth (inches)	2.3228 inch
Height	80.1 mm	Height (inches)	3.1535 inch
Width	49 mm	Width (inches)	1.9291 inch
Net weight	330 g		

Temperatures

Storage temperature	Operating temperature	-5 °C...50 °C
---------------------	-----------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Dimensions of live conductors

Type of conductor	Insulated conductor only	Round conductor	18.50 mm
Installation location	Indoor use		

Electrical attributes

Tolerance class	1	Secondary current	0...1 A
Load	0.3 VA	Primary current	100 A

Technical properties

Cable length	2.5 m	Protection degree	IP20
Nominal frequency	50 Hz		

Insulation coordination

Tolerance class	1
-----------------	---

Classifications

ETIM 8.0	EC002048	ETIM 9.0	EC002048
ETIM 10.0	EC002048	ECLASS 14.0	27-21-09-02
ECLASS 15.0	27-21-09-02		

KCMA-18-100-1A-0.3VA-1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

