

**KCMA-42-400-5A-5VA-1**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image, Similar to illustration**

Current transformers for retrofitting

Features:

- especially suitable for use in hard-to-reach places
- no cutting of the primary conductors necessary
- Unfolding of the current transformer without additional tools

**General ordering data**

Version	Primary current: 400 A, Secondary current max.: 5 A, Load: 5 VA, Tolerance class: 1, Split-core current transformer
Order No.	<a href="#">2753240000</a>
Type	KCMA-42-400-5A-5VA-1
GTIN (EAN)	4050118896718
Qty.	1 items
Manufacturer	MBS AG

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	69 mm	Depth (inches)	2.7165 inch
Height	96 mm	Height (inches)	3.7795 inch
Width	67 mm	Width (inches)	2.6378 inch
Net weight	381 g		

**Temperatures**

Storage temperature	Operating temperature	-5 °C...50 °C
---------------------	-----------------------	---------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Dimensions of live conductors**

Type of conductor	Insulated conductor only	Round conductor	42.00 mm
Installation location	Indoor use		

**Electrical attributes**

Tolerance class	1	Secondary current	0...5 A
Load	5 VA	Primary current	400 A

**Technical properties**

Cable length	0.5 m	Protection degree	IP20
--------------	-------	-------------------	------

**Insulation coordination**

Tolerance class	1
-----------------	---

**Classifications**

ETIM 8.0	EC002048	ETIM 9.0	EC002048
ETIM 10.0	EC002048	ECLASS 14.0	27-21-09-02
ECLASS 15.0	27-21-09-02		

