

KCMA-42-400-5A-5VA-1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image, Similar to illustration



Current transformers for retrofitting

Features:

- especially suitable for use in hard-to-reach places
- no cutting of the primary conductors necessary
- Unfolding of the current transformer without additional tools

General ordering data

| | |
|--------------|---|
| Version | Primary current: 400 A, Secondary current max.: 5 A, Load: 5 VA, Tolerance class: 1, Split-core current transformer |
| Order No. | 2753240000 |
| Type | KCMA-42-400-5A-5VA-1 |
| GTIN (EAN) | 4050118896718 |
| Qty. | 1 items |
| Manufacturer | MBS AG |

KCMA-42-400-5A-5VA-1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|-------|-----------------|-------------|
| Depth | 69 mm | Depth (inches) | 2.7165 inch |
| Height | 96 mm | Height (inches) | 3.7795 inch |
| Width | 67 mm | Width (inches) | 2.6378 inch |
| Net weight | 381 g | | |

Temperatures

| | | |
|---------------------|-----------------------|---------------|
| Storage temperature | Operating temperature | -5 °C...50 °C |
|---------------------|-----------------------|---------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Dimensions of live conductors

| | | | |
|-----------------------|--------------------------|-----------------|----------|
| Type of conductor | Insulated conductor only | Round conductor | 42.00 mm |
| Installation location | Indoor use | | |

Electrical attributes

| | | | |
|-----------------|------|-------------------|---------|
| Tolerance class | 1 | Secondary current | 0...5 A |
| Load | 5 VA | Primary current | 400 A |

Technical properties

| | | | |
|--------------|-------|-------------------|------|
| Cable length | 0.5 m | Protection degree | IP20 |
|--------------|-------|-------------------|------|

Insulation coordination

| | |
|-----------------|---|
| Tolerance class | 1 |
|-----------------|---|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002048 | ETIM 9.0 | EC002048 |
| ETIM 10.0 | EC002048 | ECLASS 14.0 | 27-21-09-02 |
| ECLASS 15.0 | 27-21-09-02 | | |

