

CH-SMC-00.33-Y2C180


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Base counter, gateway, control box and overvoltage protection device are connected with pre-assembled cable sets as point-to-point or Y-assembly. Weidmüller offers the right connection solutions for this, conforming to FNN and DIN-VDE 0603 standards. Pre-assembled power cables with 6kV overvoltage protection round up the portfolio.

General ordering data

Version	Smart Metering Cable Assemblies, 6 kV, Pin, Socket connector, IP20, 600 V, KB PUR US 2X1.5 GY XX 6KV, 0.53 m
Order No.	2775940033
Type	CH-SMC-00.33-Y2C180
GTIN (EAN)	4064675041504
Qty.	10 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Diameter	6.4 mm	Net weight	5.6 g
----------	--------	------------	-------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General Technical Data

Number of poles	2	Rated impulse withstand voltage	6 kV
Nominal voltage	600 V	Nominal current	18.5 A
Protection degree	IP20		

Technical Specifications Connector

Connector	Number of poles	2
	Number of poles	2
	Number of poles	2

Technical specifications for cable

Cable length	0.53 m	Line type	KB PUR US 2X1.5 GY XX 6KV
Sheathing colour	grey	Resistance to oils	Yes
Core cross-section	1.5 mm ²	Number of wires	2
Shielded	No	Halogen	No
Insulation	PP	Temperature range, moving, max.	90 °C
Temperature range, moving, min.	-30 °C	Temperature range, stationary, max.	90 °C
Temperature range, stationary, min.	-40 °C	Cable Material	PUR/ TPE
Bending radius, min., moving	15 x cable diameter	Bending radius, min., stationary	10 x cable diameter
Cable length, string 2	0.2 m	Cable length, string 1	0.33 m
Outside diameter	6.4 mm ± 0.25 mm		

Classifications

ETIM 8.0	EC001576	ETIM 9.0	EC001576
ETIM 10.0	EC001576	ECLASS 14.0	27-06-04-02
ECLASS 15.0	27-06-04-02		

