

CABTITE EP 24/32 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Cabtite - Cable Entry Plates

Insert cables and wires without plugs into control cabinets, enclosures or machines in the smallest of spaces, easily and in a space-saving manner.

With the Cabtite cable entry plates, you can do this even in harsh environments, whether protective hoses, pneumatic/hydraulic hoses or fiber optic cables - you can install your cables quickly, easily and in a space-saving manner. The installation is done through only one rectangular wall cut-out and is therefore up to 40% faster in the installation time (compared to standard cable glands).

The IP66 screw version of cable entry plates are tested according to DIN EN 60529 and made of UL94 V-0 certified TPE material with hard plastic core, suitable for the temperature range from -40°C to +90°C.

Cabtite cable entry plates are an economical alternative to conventional cable glands.

General ordering data

| | |
|------------|--|
| Version | Cable entry plate, Cabtite (cable entry system), TPE, grey, Height: 58 mm, Width: 149.6 mm, Depth: 17.3 mm, -40 °C...90 °C, IP66 |
| Order No. | 2779380000 |
| Type | CABTITE EP 24/32 GY |
| GTIN (EAN) | 4064675048954 |
| Qty. | 10 items |

CABTITE EP 24/32 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E223801

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 17.3 mm | Depth (inches) | 0.6811 inch |
| Height | 58 mm | Height (inches) | 2.2835 inch |
| Width | 149.6 mm | Width (inches) | 5.8898 inch |
| Net weight | 36.34 g | | |

Temperatures

Operating temperature -40 °C...90 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

General information

| | | | |
|---------------------------|--------|-----------------------|--------------------------|
| Tightening torque | 3.5 Nm | Silicone | No |
| UL 94 flammability rating | V-0 | Protection degree | IP66 |
| Basic material | TPE | Protection class (UL) | Type 1, Type 12, Type 4X |

Number of connectable cables

| | | | |
|------------------------------|----------------------|-------------|--|
| Type of mounting | 4 screws | | |
| Number of connectable cables | 32 | | |
| Cable entries | Number | 32 | |
| | Cable diameter, min. | 3.2 mm | |
| | Cable diameter, max. | 6.3 mm | |
| | Cable type | Round cable | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002624 | ETIM 9.0 | EC002624 |
| ETIM 10.0 | EC002624 | ECLASS 14.0 | 27-18-28-15 |
| ECLASS 15.0 | 27-18-28-15 | | |

CABTITE EP 24/32 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

