Data sheet

HDC-C-HE-SM0.3KO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Heavy-duty connectors, Crimp contact, HE, Male, Conductor cross-section, max.: 0.3, turned, Copper alloy
Order No.	2784140000
Type	HDC-C-HE-SM0.3KO
GTIN (EAN)	4064675060888
Qty.	10 items

Data sheet

HDC-C-HE-SM0.3KO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform

Dimensions and weights

Net weight	50 g

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

General data

Contact diameter, male Ø	2.48 mm	Stripping length, rated connection	7.5 mm
Type of connection	Crimp connection	Version insert	HE
Conductor cross-section, max.	0.3 mm²	Conductor cross-section, min.	0.3 mm²
Surface finish	Constantan	Plugging cycles	≥ 500
Type	Male	Basic material	Copper alloy
Series	HE	Production methods	turned
Cross-section for connected wire	0.3 - 0.3 mm²	Material of contact	Copper alloy

Classifications

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		