

## HDC-C-HE-BM0.5KO

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Version	Heavy-duty connectors, Crimp contact, HE, Female, Conductor cross-section, max.: 0.5, turned, Copper alloy
Order No.	<a href="#">2784160000</a>
Type	HDC-C-HE-BM0.5KO
GTIN (EAN)	4064675060895
Qty.	10 items

## HDC-C-HE-BM0.5KO

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Net weight 1.58 g

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

### General data

Contact diameter, male Ø	2.48 mm	Stripping length, rated connection	7.5 mm
Type of connection	Crimp connection	Version insert	HE
Conductor cross-section, max.	0.5 mm <sup>2</sup>	Conductor cross-section, min.	0.5 mm <sup>2</sup>
Surface finish	Constantan	Plugging cycles	≥ 500
Type	Female	Basic material	Copper alloy
Series	HE	Production methods	turned
Cross-section for connected wire	0.5 - 0.5 mm <sup>2</sup>	Material of contact	Copper alloy

### Classifications

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		