

HDC-C-HE-BM0.5FE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Heavy-duty connectors, Crimp contact, HE, Female, Conductor cross-section, max.: 0.5, turned, Iron
Order No.	2784200000
Type	HDC-C-HE-BM0.5FE
GTIN (EAN)	4064675061137
Qty.	10 items

HDC-C-HE-BM0.5FE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 1.5 g

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

General data

Contact diameter, male Ø	2.48 mm	Stripping length, rated connection	7.5 mm
Type of connection	Crimp connection	Version insert	HE
Conductor cross-section, max.	0.5 mm ²	Conductor cross-section, min.	0.5 mm ²
Surface finish	all others	Plugging cycles	≥ 500
Type	Female	Basic material	Iron
Series	HE	Production methods	turned
Cross-section for connected wire	0.5 - 0.5 mm ²	Material of contact	Iron

Classifications

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		