

VGM32-MS65 3X7.6 SL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

| | |
|------------|--|
| Version | Cable glands, Cable glands, M 32, 7.5 mm, Brass, nickel-plated |
| Order No. | 2784960000 |
| Type | VGM32-MS65 3X7.6 SL |
| GTIN (EAN) | 4064675061533 |
| Qty. | 25 items |

VGM32-MS65 3X7.6 SL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

Net weight 43.94 g

Temperatures

Operating temperature -40 °C...135 °C

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | b5ff1f66-ddba-4739-9fc0-0521ddb52139 |

General information

| | | | |
|--------------------------------------|----------------------|--------------------------------------|----------|
| UL 94 flammability rating | V-0 | AF size | 36 mm |
| Protection degree | IP65 | Cable gland | M 32 |
| Basic material | Brass, nickel-plated | Seal insert | TPE |
| Notch multi-layer sealing diameter 1 | 7.6 mm | Notch multi-layer sealing diameter 2 | 7.6 mm |
| Notch multi-layer sealing diameter 3 | 7.6 mm | External thread | M 32 |
| Length of thread | 7.5 mm | Width, outer dimension C | 38.50 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000441 | ETIM 9.0 | EC000441 |
| ETIM 10.0 | EC000441 | ECLASS 14.0 | 27-14-08-01 |
| ECLASS 15.0 | 27-14-08-01 | | |

