

VGM32-MS65 3X6.7 SL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Cable glands, Cable glands, M 32, 7.5 mm, Brass, nickel-plated
Order No.	2784970000
Type	VGM32-MS65 3X6.7 SL
GTIN (EAN)	4064675061540
Qty.	25 items

VGM32-MS65 3X6.7 SL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

Net weight 43.86 g

Temperatures

Operating temperature -40 °C...135 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

General information

UL 94 flammability rating	V-0	AF size	36 mm
Protection degree	IP65	Cable gland	M 32
Basic material	Brass, nickel-plated	Seal insert	TPE
Notch multi-layer sealing diameter 1	6.7 mm	Notch multi-layer sealing diameter 2	6.7 mm
Notch multi-layer sealing diameter 3	6.7 mm	External thread	M 32
Length of thread	7.5 mm	Width, outer dimension C	38.50 mm

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		

VGM32-MS65 3X6.7 SL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

