

**IE-ANT-CELL-MIMO-DO-SMAM****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Antennas and antenna accessories (coax cables and mounts)

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

**General ordering data**

Version	Omni-directional antenna, Cellular antenna, Up to 5G (NR), Linear, Vertical, 2x SMA male, IP67, Impedance: 50 Ω
Order No.	<a href="#">2788120000</a>
Type	IE-ANT-CELL-MIMO-DO-SMAM
GTIN (EAN)	4064675066385
Qty.	1 items

## IE-ANT-CELL-MIMO-DO-SMAM

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Height	100 mm	Height (inches)	3.937 inch
Net weight	463 g		

## Temperatures

Storage temperature	Operating temperature	-40 °C...85 °C
---------------------	-----------------------	----------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	e4cad7fc-a55e-4d5c-8f05-417a6385e9b6

## Enclosure material

Colour	black
--------	-------

## Included in delivery

Included in delivery	1 x antenna
----------------------	-------------

## Mechanical and material properties of cable

Cable length	1 m	Min. bending radius, repetitive	25 mm
--------------	-----	---------------------------------	-------

## Technical data

Type of connection	2x SMA male	Amount of antenna elements (MIMO)	2
Impedance	50 Ω	Standing wave ratio	<2.0 typical, 3.0 max.
Composite power max.	50 W	Frequency range	690-950 MHz, 1.7-3.8 GHz
Antenna gain	2.5 dBi	Polarisation	Linear, Vertical

## Environmental conditions

Operating temperature, max.	85 °C	Operating temperature, min.	-40 °C
-----------------------------	-------	-----------------------------	--------

## Classifications

ETIM 8.0	EC001698	ETIM 9.0	EC001698
ETIM 10.0	EC001698	ECLASS 14.0	19-07-01-07
ECLASS 15.0	19-07-01-07		

## IE-ANT-CELL-MIMO-DO-SMAM

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Antennas and antenna accessories (coax cables and mounts)



Antennas and antenna accessories (coax cables and mounts)

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

## General ordering data

Type	IE-CC-SMAM-SMAF-1M	Version
Order No.	<a href="#">2787920000</a>	Antenna cable, Connection 1.: SMA male, Connection 2.: SMA
GTIN (EAN)	4064675066088	female, Length: 1 m
Qty.	1 ST	
Type	IE-CC-SMAM-SMAF-3M	Version
Order No.	<a href="#">2787930000</a>	Antenna cable, Connection 1.: SMA male, Connection 2.: SMA
GTIN (EAN)	4064675066095	female, Length: 3 m
Qty.	1 ST	
Type	IE-CC-SMAM-SMAF-5M	Version
Order No.	<a href="#">2787940000</a>	Antenna cable, Connection 1.: SMA male, Connection 2.: SMA
GTIN (EAN)	4064675066200	female, Length: 5 m
Qty.	1 ST	