

BEP 2C 4

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



General ordering data

Version	B-series, End plate
Order No.	2790960000
Type	BEP 2C 4
GTIN (EAN)	4064675070153
Qty.	50 items
Local product	Only available in certain countries

BEP 2C 4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

General ordering data

Local product Only available in certain countries

Dimensions and weights

Depth	30.5 mm	Depth (inches)	1.2008 inch
Height	55 mm	Height (inches)	2.1654 inch
Width	1.5 mm	Width (inches)	0.0591 inch
Net weight	2.13 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Material data

Basic material	PA 66/6	Colour	grey
UL 94 flammability rating	V-0		

Additional technical data

Snap-on Yes

Classifications

ETIM 8.0	EC000886	ETIM 9.0	EC000886
ETIM 10.0	EC000886	ECLASS 14.0	27-25-03-01
ECLASS 15.0	27-25-03-01		