

## BEP 2C 6 BL

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Version	B-series, End plate
Order No.	<a href="#">2790990000</a>
Type	BEP 2C 6 BL
GTIN (EAN)	4064675070184
Qty.	50 items
Local product	Only available in certain countries

**BEP 2C 6 BL**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**General ordering data**

Local product Only available in certain countries

**Dimensions and weights**

Depth	35.5 mm	Depth (inches)	1.3976 inch
Height	62 mm	Height (inches)	2.4409 inch
Width	1.5 mm	Width (inches)	0.0591 inch
Net weight	2.65 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Material data**

Basic material	PA 66/6	Colour	blue
UL 94 flammability rating	V-0		

**Additional technical data**

Snap-on Yes

**Classifications**

ETIM 8.0	EC000886	ETIM 9.0	EC000886
ETIM 10.0	EC000886	ECLASS 14.0	27-25-03-01
ECLASS 15.0	27-25-03-01		