

BEP 2T 2.5 BL



General ordering data

| | |
|---------------------|---|
| Version | B-series, End plate |
| Order No. | 2791170000 |
| Type | BEP 2T 2.5 BL |
| GTIN (EAN) | 4064675070368 |
| Qty. | 50 items |
| Delivery status | This article will no longer be available in the future. |
| Available until | 2025-12-31T00:00:00+01:00 |
| Alternative product | BEP 2T 2.5N BL |
| Local product | Only available in certain countries |

Technical data

Approvals

ROHS Conform

General ordering data

Local product Only available in certain countries

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 42 mm | Depth (inches) | 1.6535 inch |
| Height | 73 mm | Height (inches) | 2.874 inch |
| Width | 1.5 mm | Width (inches) | 0.0591 inch |
| Net weight | 3.09 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 120 °C | | |

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Material data

| | | | |
|---------------------------|---------|--------|------|
| Basic material | PA 66/6 | Colour | blue |
| UL 94 flammability rating | V-0 | | |

Additional technical data

Snap-on Yes

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000886 | ETIM 9.0 | EC000886 |
| ETIM 10.0 | EC000886 | ECLASS 14.0 | 27-25-03-01 |
| ECLASS 15.0 | 27-25-03-01 | | |