


BCC 6/2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Cross-connector (terminal), Plugged, orange, 4 1 A, Number of poles: 2, Pitch in mm (P): 8.00, Insulated: Yes, Width: 13 mm
Order No.	2791260000
Type	BCC 6/2
GTIN (EAN)	4064675070450
Qty.	100 items
Local product	Only available in certain countries

BCC 6/2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

General ordering data

Local product	Only available in certain countries
---------------	-------------------------------------

Dimensions and weights

Depth	2.5 mm	Depth (inches)	0.0984 inch
Height	28 mm	Height (inches)	1.1024 inch
Width	13 mm	Width (inches)	0.5118 inch
Net weight	2.2 g		

Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-50 °C...120 °C
---------------------	----------------	-----------------------	-----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	PA 66/6	Colour	orange
UL 94 flammability rating	V-0		

Additional technical data

Type of fixing	Plugged	Explosion-tested version	Yes
----------------	---------	--------------------------	-----

Dimensions

Pitch in mm (P)	8.00 mm
-----------------	---------

General

Number of poles	2
-----------------	---

Rating data

Nominal current	41 A
-----------------	------

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		