

## BCC 6/10

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Version	Cross-connector (terminal), Plugged, orange, 41 A, Number of poles: 10, Pitch in mm (P): 8.00, Insulated: Yes, Width: 78 mm
Order No.	<a href="#">2791290000</a>
Type	BCC 6/10
GTIN (EAN)	4064675070481
Qty.	10 items
Local product	Only available in certain countries

## BCC 6/10

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### General ordering data

Local product	Only available in certain countries
---------------	-------------------------------------

### Dimensions and weights

Depth	2.5 mm	Depth (inches)	0.0984 inch
Height	28 mm	Height (inches)	1.1024 inch
Width	78 mm	Width (inches)	3.0709 inch
Net weight	14.35 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-50 °C...120 °C
---------------------	----------------	-----------------------	-----------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	PA 66/6	Colour	orange
UL 94 flammability rating	V-0		

### Additional technical data

Type of fixing	Plugged	Explosion-tested version	Yes
----------------	---------	--------------------------	-----

### Dimensions

Pitch in mm (P)	8.00 mm
-----------------	---------

### General

Number of poles	10
-----------------	----

### Rating data

Nominal current	41 A
-----------------	------

### Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		