



Insulated ring-cable connector made from PVC

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 1.5 mm ² , 0.5 mm ² - 1.5 mm ²
Order No.	2792000000
Type	LIR 1,5M10 V
GTIN (EAN)	4064675073192
Qty.	100 items

LIR 1,5M10 V

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	5.9 mm	Depth (inches)	0.2323 inch
Width	28.1 mm	Width (inches)	1.1063 inch
Net weight	0.01 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Insulated ring-cable connector 1.5 mm ² / M10
------------------------	---

Connectors

Conductor cross-section, max.	1.5 mm ²	Conductor cross-section, min.	0.5 mm ²
Conductor cross-section	1.5 mm ²	Insulation	Available, PVC
Dimension (bolt)	M 10	Dimension	M 10
Material/plastic	PVC	Identification colour	red
Connection density (S1)	0.75 mm	Inside diameter (d1)	10.5 mm
Plastic collar length (b)	11.3 mm	Plastic collar diameter (D)	4 mm
Outside diameter (d)	14 mm		

Classifications

ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 14.0	27-40-02-92
ECLASS 15.0	27-40-02-92		