

## CUTFIX PRO

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- For automatically cutting individual wires to length
- High repeat accuracy due to the precise servo DC drive
- Interface for controlling the automatic cutter via an IBM-compatible PC

### General ordering data

Version	Automatic machines, Cutting machine
Order No.	<a href="#">2797190000</a>
Type	CUTFIX PRO
GTIN (EAN)	4064675213192
Qty.	1 items

**CUTFIX PRO**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Depth	250 mm	Depth (inches)	9.8425 inch
Height	250 mm	Height (inches)	9.8425 inch
Width	300 mm	Width (inches)	11.811 inch
Net weight	11000 g		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

**Automatic cutting**

Connected load	0.1 kW	Amount pre-selection, max.	Adjustable part quantity code
Drive	electrical	Keyboard	Touch display
Indicator display	LCD display	Length pre-selection, max.	999999 mm
Length pre-selection, min.	10 mm	Software	for data exchanging with IBM-compatible PC
Aperture (max. diameter)	8 mm outer diameter	Electrical connection	100 - 240 V AC / 50/60 Hz
Flexible/solid individual conductors	max. 10 mm <sup>2</sup> / max. 2.5 mm <sup>2</sup>		

**Classifications**

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		