

THM MT30X 25.4/12.7 TR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

General ordering data

Version	THM, Device markers, 12.7 x 25.4 mm, Transparent
Order No.	2798960000
Type	THM MT30X 25.4/12.7 TR
GTIN (EAN)	4064675259886
Qty.	10000 items

THM MT30X 25.4/12.7 TR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.0031 inch
Height	12.7 mm	Height (inches)	0.5 inch
Width	25.4 mm	Width (inches)	1 inch
Net weight	0.07 g		

Temperatures

Operating temperature range -40...150 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Adhesive	Acrylate adhesive		
Version	Self-adhesive		
Width	25.4 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Colour	Transparent		
Halogen	No		
Basic material	Polyester		
Printed characters	without		
Number of markers per packaging unit compatible printer	Form of supply	Label reel	
Number of markers per combination	1 Label reel = Device markers		
Operating temperature range	-40...150 °C		
Number per roll	10000		

Device markers

Halogen No

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Drawings

