

**EL KSM 10.6 MM WS 30M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**MultiMark MultiFit**

For connectors from competitors.

The elastic surface finish makes for simple installation.

This special material enables the strips to be stretched to accommodate slight variations in spacing, especially with long terminal blocks.

A print resolution of 300 dpi also produces a very legible script. Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

**General ordering data**

|            |                                     |
|------------|-------------------------------------|
| Version    | Terminal marker, 10.6 x 5 mm, white |
| Order No.  | <a href="#">2799270000</a>          |
| Type       | EL KSM 10.6 MM WS 30M               |
| GTIN (EAN) | 4064675261032                       |
| Qty.       | 1 items                             |

**EL KSM 10.6 MM WS 30M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)
**Technical data****Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |         |                 |                |
|------------|---------|-----------------|----------------|
| Depth      | 0.7 mm  | Depth (inches)  | 0.0276 inch    |
| Height     | 10.6 mm | Height (inches) | 0.4173 inch    |
| Width      | 5 mm    | Width (inches)  | 0.1968 inch    |
| Length     | 30 m    | Length (inches) | 1181.1024 inch |
| Net weight | 240 g   |                 |                |

**Temperatures**

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -50...100 °C |
|-----------------------------|--------------|

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**General data**

|                                   |               |                                   |              |
|-----------------------------------|---------------|-----------------------------------|--------------|
| Version                           | halogen-free  | Width                             | 5 mm         |
| UL 94 flammability rating         | V-2           | Operating temperature range, max. | 100 °C       |
| Operating temperature range, min. | -50 °C        | Colour                            | white        |
| Halogen                           | No            | Length                            | 30 m         |
| Basic material                    | Polypropylene | Operating temperature range       | -50...100 °C |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000761    | ETIM 9.0    | EC000761    |
| ETIM 10.0   | EC000761    | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 |             |             |

