

PC RC M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Protective caps suitable for FieldPower and WIPL family
with round connector

General ordering data

Order No.	2820090000
Type	PC RC M
GTIN (EAN)	4064675591405

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E307231

Dimensions and weights

Net weight	3 g
------------	-----

Temperatures

Storage temperature		Ambient temperature	-25 °C...125 °C
Operating temperature	-40 °C...85 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical specifications for cable

Insulation voltage	<500 V (housing/PE)
--------------------	---------------------

General technical data

Housing main material	PA 66	Protection degree	IP67
-----------------------	-------	-------------------	------

General standards

Certificate no. (cULus)	E307231
-------------------------	---------

General data

UL 94 flammability rating	V-2	Protection degree	IP67
---------------------------	-----	-------------------	------

Classifications

ETIM 8.0	EC002314	ETIM 9.0	EC002314
ETIM 10.0	EC002314	ECLASS 14.0	27-44-02-08
ECLASS 15.0	27-44-02-08		

PC RC M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Plug connector - screw system



The circular connectors with screw system are characterised by their compact design. This allows them to be used in a wide range of applications and industries. They are available both as plugs and sockets.

General ordering data

Type	RC F P2 SP	Version	
Order No.	2903200000		
GTIN (EAN)	4099986 122376		
Qty.			

DC connectors



The circular connectors with screw system are characterised by their compact design. This allows them to be used in a wide range of applications and industries. They are available both as plugs and sockets.

General ordering data

Type	RC F P2 M20 SP	Version	
Order No.	2860640000		
GTIN (EAN)	4064675576655		
Qty.			