

SFX-M 11/60-5 LRP AL SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	MetalliCard, Conductor and cable markers, 7 - 40 mm, 60 x 11 mm, To customer specification
Order No.	2859580000
Type	SFX-M 11/60-5 LRP AL SDR
GTIN (EAN)	4064675572367
Qty.	1 items

SFX-M 11/60-5 LRP AL SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.8 mm	Depth (inches)	0.0315 inch
Height	60 mm	Height (inches)	2.3622 inch
Width	11 mm	Width (inches)	0.4331 inch
Net weight	0.85 g		

Temperatures

Operating temperature range	-55...130 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Number per sheet	1	
Type of printing	To customer specification	
Version	halogen-free	
Width	11 mm	
Operating temperature range, max.	130 °C	
Operating temperature range, min.	-55 °C	
Colour	To customer specification	
Basic material	Anodized aluminium	
Printed characters	Requires M-Print PRO File	
Number of markers per packaging unit	Form of supply	MetalliCard
Size of labelling field	11.2 x 45 mm	
Recommended industries compatible printer	Process, Energy	
Number of markers per combination	1 MetalliCard = Conductor and cable markers	
Operating temperature range	-55...130 °C	

Conductor and cable markers

Conductor cross-section, max.	500 mm ²	Conductor cross-section, min.	16 mm ²
Conductor O.D., max.	40 mm	Conductor O.D., min.	7 mm
Cable tie passage	Flat	Conductor O.D.	7 - 40 mm
Cross-section for connected wire	16 - 500 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

SFX-M 11/60-5 LRP AL SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

