

**CC-M 15/45 2X3 LRP ST**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



**General ordering data**

Version	MetalliCard, Device markers, 15 x 45 mm, silver
Order No.	<a href="#">2863780000</a>
Type	CC-M 15/45 2X3 LRP ST
GTIN (EAN)	4064675597322
Qty.	500 items
Delivery status	This article will no longer be available in the future.
Last order date	2025-06-30T00:00:00+02:00

**CC-M 15/45 2X3 LRP ST**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	0.5 mm	Depth (inches)	0.0197 inch
Height	15 mm	Height (inches)	0.5906 inch
Width	45 mm	Width (inches)	1.7716 inch
Net weight	3.43 g		

**Temperatures**

Operating temperature range -55...130 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Version	pluggable, with 3.5 mm mounting hole		
Width	45 mm		
Operating temperature range, max.	130 °C		
Operating temperature range, min.	-55 °C		
Colour	silver		
Basic material	Stainless steel 1.4301		
Printed characters	neutral		
Number of markers per packaging unit	Form of supply	MetalliCard	
Size of labelling field	15.2 x 42.2 mm		
compatible printer			
Number of markers per combination	1 MetalliCard = Device markers		
Operating temperature range	-55...130 °C		

**Device markers**

Drill-hole diameter 3.30 mm

**Classifications**

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

**CC-M 15/45 2X3 LRP ST**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

