

## U-LINK-CNSERVER-1Y

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Example of use



The Weidmüller u-link remote access service offers an easy possibility to securely access ethernet devices in a remote network.

With the u-link VPN Server as the central meeting point server, the VPN clients (service PC and Weidmüller u-link client devices) always connect outbound and thus conform to the typical IT security requirements.

Separate database and server instances are used for each u-link customer account (secure client isolation) to ensure data integrity.

Communication between the u-link VPN server and remote clients (service PCs and u-link client devices) takes place via a certificate-protected openVPN connection. The u-link creed is "configuration instead of programming" the use is intuitive and does not require expert knowledge.

#### Featureset:

- 1-click VPN remote access for service PC's
- easyAccess: web, rdp or vnc connections to remote hosts fully browser based for use with tablet or smartphone
- Organization and Group Management
- Topologies including 3rd party end-devices
- Firmware management: Display of firmware status of all routers and the option of a time-controlled, automated firmware update
- Individual access rights: granular configuration of access rights to devices in the target network

- Extensive event log: Presentation of all activities in the u-link portal with extensive filter and export functions
- Password policy: Increased security through configurable specification of minimum requirements for password quality and validity period

Weidmüller offers the following usage variations and additional options for the u-link Remote Access Service:

#### Basic version:

- Automatically assigned by registering at [u-link.weidmueller.com](http://u-link.weidmueller.com)
- Free use for 6 months, extended to 365 days when registering a new u-link client device
- Full featureset
- Unlimited users
- Max. 50 u-link capable devices (access points to a remote network)
- 1 simultaneous VPN connection
- No data or speed limitations (subject to normal market usage)

#### Extensions

- Additional 50/100/250/500/1000 or more u-link capable devices
- Additional simultaneous VPN connections
- China-VPN: secure and reliable VPN connection to and from China

## U-LINK-CNSERVER-1Y

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

---

### General ordering data

Version	License code for u-link Remote Access Service., Allows the use of the server in China for a secure and reliable VPN connection to and from China.
Order No.	<a href="#">2870140000</a>
Type	U-LINK-CNSERVER-1Y
Qty.	1 items

**U-LINK-CNSERVER-1Y**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Net weight 0 g

**Temperatures**

Storage temperature Operating temperature

**Environmental Product Compliance**

RoHS Compliance Status Not affected  
 REACH SVHC No SVHC above 0.1 wt%

**Functions and features**

Period	1 year from activation of the license key or expiry of the existing license. The individual license term is visible during activation.	China-VPN	Reliable VPN connection to and from China
--------	--	-----------	---

**System requirements**

Hardware, remote target network	Weidmüller hardware with u-link VPN client	Hardware (service PC)	PC with operating system Windows 7, 8, 10 or 11
Portal administration (user/device configuration)	via Webbrowser (HTTPS), login via username and password	VPN software (service PC)	u-link VPN-client (installation on PC)

**Miscellaneous**

Activation	Client account administrator enters the licence key in the u-link portal (functions immediately available)	Included in delivery	Email with license key
------------	--	----------------------	------------------------

**Classifications**

ETIM 8.0	EC000809	ETIM 9.0	EC000809
ETIM 10.0	EC000809	ECLASS 14.0	27-24-25-01
ECLASS 15.0	27-24-25-01		