

## IE-SR-4GT-LTE/4G-EU

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



### Weidmüller Industrial Security Routers

- Secure networks
  - Stateful packet inspection Firewall
  - IP/Port- forwarding
  - Network segmentation
- Easy integration of machine networks into manufacturing networks through 1: 1 NAT
- Secure and easy remote maintenance with Weidmüller u-link remote access service
- Enable modular and future proof network architectures with static and dynamic routing
- Secure communication over the Internet by using IPsec and OpenVPN
- Reliable internet connection, even without on-site internet access, thanks to integrated 4G/LTE cellular modem
- Full flexibility thanks to Fast Ethernet and Gigabit Ethernet interfaces ranging from 2 up to 4 ports.

### General ordering data

Version	Security/NAT/VPN/U-link Router, with integrated multi-band modem (4G/3G/2G), EU-model, Gigabit Ethernet, 4x RJ45 10/100/1000BaseT(X), IP20, -25 °C...70 °C
Order No.	<a href="#">2873920000</a>
Type	IE-SR-4GT-LTE/4G-EU
GTIN (EAN)	4064675647683
Qty.	1 items

**IE-SR-4GT-LTE/4G-EU**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E141197

**Dimensions and weights**

Depth	115 mm	Depth (inches)	4.5275 inch
Height	150 mm	Height (inches)	5.9055 inch
Width	35 mm	Width (inches)	1.378 inch
Net weight	632 g		

**Temperatures**

Storage temperature	-40 °C...85 °C	Operating temperature	-25 °C...70 °C
Humidity	5 - 90 %, no condensation		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption		
RoHS Exemption (if applicable/known)	6c, 7a, 7cl, 7cll		
REACH SVHC	Lead 7439-92-1		
SCIP	1bb4009c-24f3-4115-ab13-f6bde3580fe2		

**Mobile radio interface**

Transmission rate mobile radio	LTE category	CAT 4
	Download rate, max.	150 Mbit/s
	Upload rate, max.	50 Mbit/s
Mode of operation	Permanent connection, Manual connection control via web interface, Fallback	
Wireless module	multi-band modem (4G/3G/2G)	
Frequency band	LTE-FDD: B1,B3,B7,B8,B20,B28, LTE-TDD: B38, B40, B41, WCDMA: B1,B5,B8, GSM/GPRS/EDGE: 850,900,1800 MHz	

**EMC conformity and approvals**

EMC standards	EN 61000-6-4, EN 61000-6-2	Vibration	according to IEC 60068-2-6
Shock	according to IEC 60068-2-27	Safety standard	EN 62368-1, EN 62311, UL 61010-1, UL 61010-2-201
Security standard	EN 18031-1		

**Environmental conditions**

Operating temperature, max.	70 °C		
Operating temperature, min.	-25 °C		
Humidity	5 - 90 %, no condensation		
Storage temperature, max.	85 °C		
Storage temperature, min.	-40 °C		
Operating altitude	Altitude, max.	2000 m	
	Note	in acc. with UL	

## IE-SR-4GT-LTE/4G-EU

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Guarantee

Time interval	3 years
---------------	---------

## Interfaces

RJ45 ports	10/100/1000BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port	Number of ports	4x RJ45 10/100/1000BaseT(X)
Function reset button	Restoration of factory settings	Digital outputs	Alarm: indicates a configurable network state or fault (24 V out), VPN-active: indicates an active VPN connection (24 V out), 1x
Digital inputs	2x, galvanically isolated, VPN-initiate: establishes a pre-configured VPN connection (24 V in), Cut: physically disconnects (Link Down) the WAN port (24 V in), Trigger pre-configured packet filter rules (24 V in)	SCM-Card slot type	Smart Card (ID-000 format), Save and restore the configuration using smart card (memory chip)
SIM-Card slot type	Mini-SIM (ID-000 format)	Connector for external antennas	2x SMA female
USB port	USB 2.0 interface for firmware update or restoration of the device configuration via USB flash drive	Serial port	1x RS-485, 2-wire, galvanically isolated, 1 removable 3-pole terminal block
Number of SIM-Card slots	1	Number of SCM-Card slots	1
LED indicator	Power: indicates power supply status, boot-up process, firmware update process, Status: indicates system status, VPN: indicates VPN tunnel status, LTE/4G: indicates mobile radio connection status, Port LED: Link/ACT, Speed (RJ45 port)		

## Management features

Device configuration	Webbrowser (HTTP/HTTPS), SNMP v3, Windows tool	Monitoring function	SNMP v3, Syslog, Event based warning via E-Mail, Event based warning via relay, Event based warning via SMS
IP-address management	Static, DHCP-Client, DHCP-Server (pool-based), DNS-Relay	Time synchronization management	NTP server, NTP client

## Power supply

Reverse polarity protection	Yes	
Supply voltage	24 V DC, 1 single input	
Overload current protection	Yes	
Connection type	1 removable 4-pin terminal block	
Voltage supply range	Voltage type	DC
	Voltage, min.	19.2 V
	Voltage, max.	28.8 V

## IE-SR-4GT-LTE/4G-EU

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

Current consumption	Voltage	24 V
	Current	1.5 A

### Routing Features

NAT functions	Source / Destination NAT (Port / Host / Network)	Firewall functions	Stateful Packet Inspection Firewall (Layer-3), Transparent bridge mode (4-port switch with additional Layer-2 filter)
VPN functions	u-link client, OpenVPN (Server or Client), IPSec (Initiator or Responder)	Routing functions	IPv4 routing, IPv4 routing extended (each interface (LAN, WAN, optional cellular) can be configured as separate IP network), Static and dynamic IP Routing, RIPv2 / OSPF

### Technical data

Housing main material	Aluminium	Type of mounting	DIN rail
Protection degree	IP20	Speed	Gigabit Ethernet

### Technology

Standard	IEEE 802.3 for 10BASE-T, IEEE 802.3u for 100BASE-TX, IEEE 802.3ab for 1000BASE-T
----------	--

### Important note

Product information	For the SCM card usage please check the compatibility list for suitable router models and hardware revisions found at the SCM card IE-EBR-SMARTCARD-SR 2909820000.
---------------------	--

### Classifications

ETIM 8.0	EC001478	ETIM 9.0	EC001478
ETIM 10.0	EC001478	ECLASS 14.0	19-17-04-05
ECLASS 15.0	19-17-04-05		

## IE-SR-4GT-LTE/4G-EU

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Antennas and antenna accessories (coax cables and mounts)



Antennas and antenna accessories (coax cables and mounts)

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

## General ordering data

Type	IE-ANT-CELL/WL-MB-MIMO-...	Version
Order No.	<a href="#">2788090000</a>	Omni-directional antenna, Cellular antenna, Wi-Fi antenna, Up to 5G
GTIN (EAN)	4064675066354	(NR), Up to Wi-Fi 6 & 6E (IEEE802.11ax), Linear, Vertical, 2x SMA
Qty.	1 ST	male, 2x RP-SMA female, IP67, Impedance: 50 Ω
Type	IE-ANT-CELL-MIMO-DO-SMAM	Version
Order No.	<a href="#">2788120000</a>	Omni-directional antenna, Cellular antenna, Up to 5G (NR), Linear,
GTIN (EAN)	4064675066385	Vertical, 2x SMA male, IP67, Impedance: 50 Ω
Qty.	1 ST	
Type	IE-ANT-CELL-SISO-EO-SMAM	Version
Order No.	<a href="#">2788130000</a>	Omni-directional antenna, Cellular antenna, Up to 5G (support for
GTIN (EAN)	4064675066392	frequencies below 2.7 GHz, e.g., bands n1, n2, n28), Vertical, SMA
Qty.	1 ST	male, IP66, Impedance: 50 Ω
Type	IE-ANT-CELL-SISO-LO-NF	Version
Order No.	<a href="#">2788150000</a>	Omni-directional antenna, Cellular antenna, Up to 5G (NR), Vertical, N
GTIN (EAN)	4064675066415	female, IP66, Impedance: 50 Ω
Qty.	1 ST	

### u-link Remote Access Service



The Weidmüller u-link remote access service offers an easy possibility to securely access ethernet devices in a remote network.

With the u-link VPN Server as the central meeting point server, the VPN clients (service PC and Weidmüller u-link client devices) always connect outbound and thus conform to the typical IT security requirements. Separate database and server instances are used for each u-link customer account (secure client isolation) to ensure data integrity.

Communication between the u-link VPN server and remote clients (service PCs and u-link client devices) takes place via a certificate-protected openVPN connection. The u-link creed is "configuration instead of programming" the use is intuitive and does not require expert knowledge.

Featureset:

- 1-click VPN remote access for service PC's
- easyAccess: web, rdp or vnc connections to remote hosts fully browser based for use with tablet or smartphone
- Organization and Group Management
- Topologies including 3rd party end-devices
- Firmware management: Display of firmware status of all routers and the option of a time-controlled, automated firmware update
- Individual access rights: granular configuration of access rights to devices in the target network
- Extensive event log: Presentation of all activities in the u-link portal with extensive filter and export functions
- Password policy: Increased security through configurable specification of minimum requirements for password quality and validity period

Weidmüller offers the following usage variations and additional options for the u-link Remote Access Service:

Basic version:

- Automatically assigned by registering at u-link.weidmueller.com
- Free use for 6 months, extended to 365 days when registering a new u-link client device
- Full featureset
- Unlimited users
- Max. 50 u-link capable devices (access points to a remote network)
- 1 simultaneous VPN connection
- No data or speed limitations (subject to normal market usage)

Extensions

- Additional 50/100/250/500/1000 or more u-link capable devices
- Additional simultaneous VPN connections
- China-VPN: secure and reliable VPN connection to and from China

## IE-SR-4GT-LTE/4G-EU

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## General ordering data

Type	U-LINK-BASIC-EXTENSION...	Version
Order No.	<a href="#">3024610000</a>	License code for u-link Remote Access Service., Extends the period of
GTIN (EAN)		the basic license by 1 year.
Qty.	1 ST	
Type	U-LINK-50-DEVICES-1Y	Version
Order No.	<a href="#">2870090000</a>	License code for u-link Remote Access Service., Adds 50 additional
GTIN (EAN)		configurable u-link clients on Weidmüller hardware to the basic
Qty.	1 ST	license and extends the period of the basic license accordingly.
Type	U-LINK-100-DEVICES-1Y	Version
Order No.	<a href="#">2870100000</a>	License code for u-link Remote Access Service., Adds 100 additional
GTIN (EAN)		configurable u-link clients on Weidmüller hardware to the basic
Qty.	1 ST	license and extends the period of the basic license accordingly.
Type	U-LINK-250-DEVICES-1Y	Version
Order No.	<a href="#">2870110000</a>	License code for u-link Remote Access Service., Adds 250 additional
GTIN (EAN)		configurable u-link clients on Weidmüller hardware to the basic
Qty.	1 ST	license and extends the period of the basic license accordingly.
Type	U-LINK-500-DEVICES-1Y	Version
Order No.	<a href="#">2870120000</a>	License code for u-link Remote Access Service., Adds 500 additional
GTIN (EAN)		configurable u-link clients on Weidmüller hardware to the basic
Qty.	1 ST	license and extends the period of the basic license accordingly.
Type	U-LINK-1000-DEVICES-1Y	Version
Order No.	<a href="#">2924220000</a>	License code for u-link Remote Access Service., Adds 1000 additional
GTIN (EAN)		configurable u-link clients on Weidmüller hardware to the basic
Qty.	1 ST	license and extends the period of the basic license accordingly.
Type	U-LINK-1-CONNECTION-1Y	Version
Order No.	<a href="#">2870130000</a>	"VPN connection" licence code for u-link Remote Access Service. Can
GTIN (EAN)		be used as an additional VPN connection or to extend the period of a
Qty.	1 ST	VPN connection that has already been activated
Type	U-LINK-CNSERVER-1Y	Version
Order No.	<a href="#">2870140000</a>	License code for u-link Remote Access Service., Allows the use of the
GTIN (EAN)		server in China for a secure and reliable VPN connection to and from
Qty.	1 ST	China.

## Mounting kit for 19" rack assembly

- For assembling DIN rail-based devices on 19" racks



## General ordering data

Type	RM-KIT	Version
Order No.	<a href="#">1241440000</a>	Kit for 19"-rack mounting
GTIN (EAN)	4050118029154	
Qty.	1 ST	

**IE-SR-4GT-LTE/4G-EU**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Accessories**

**Ethernet**



- Suitable for Cat. 5 (up to 100 MHz) and Cat. 6 (up to 250 MHz Class E)
- Suitable for PoE+ (according to IEEE 802.3at, IEEE 802.3bt Type 3 and 4)
- Protection of all wire pairs
- Connection via RJ45 sockets
- Metal housing

**General ordering data**

Type	VDATA CAT6	Version	
Order No.	<a href="#">1348590000</a>		Terminal rail fixing, Surge protection, Cat.6, PoE, 802.3 bt at Type 1,
GTIN (EAN)	4050118153002		802.3 bt at Type 2, 802.3 bt at Type 3, 802.3 bt at Type 4
Qty.	1 ST		

**Industrial Security Router**



**Weidmüller Industrial Security Routers**

- Secure networks
  - Stateful packet inspection Firewall
  - IP/Port- forwarding
  - Network segmentation
- Easy integration of machine networks into manufacturing networks through 1: 1 NAT
- Secure and easy remote maintenance with Weidmüller u-link remote access service
- Enable modular and future proof network architectures with static and dynamic routing
- Secure communication over the Internet by using IPsec and OpenVPN
- Reliable internet connection, even without on-site internet access, thanks to integrated 4G/LTE cellular modem
- Full flexibility thanks to Fast Ethernet and Gigabit Ethernet interfaces ranging from 2 up to 4 ports.

**General ordering data**

Type	IE-EBR-SMARTCARD-SR	Version	
Order No.	<a href="#">2909820000</a>		Router smartcard,
GTIN (EAN)	4099986227361		
Qty.	1 ST		