Data sheet

THM SE-M 100 BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



With the neutral safety labels, standard-compliant marking in accordance with ISO 7010 can now be implemented flexibly and easily.

General ordering data

Version	Device markers, Device markers, 100 x 100 mm, blue
Order No.	2885680000
Type	THM SE-M 100 BL
GTIN (EAN)	4064675854289
Qty.	250 items

THM SE-M 100 BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	0.1 mm	Depth (inches)	0.0039 inch
Height	100 mm	Height (inches)	3.937 inch
Width	100 mm	Width (inches)	3.937 inch
Net weight	1 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Adhesive	Acrylate adhesive	Version	Self-adhesive
Width	100 mm	UL 94 flammability rating	V-0
Operating temperature range, max.	110 °C	Operating temperature range, min.	-50 °C
Colour	blue	Halogen	Yes
Basic material	Vinyl film	Printed characters	neutral
Approval acc. to UL 969	Yes		

Device markers

Halogen	Yes

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

THM SE-M 100 BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

