Data sheet

# ESG-LP 9/20 MM WS

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



## General ordering data

| | |
|---|---|
| Version | ESG, Device markers, 9 x 20 mm, white |
| Order No. | 2885840000 |
| Type | ESG-LP 9/20 MM WS |
| GTIN (EAN) | 4064675854449 |
| Qty. | 15000 items |

# ESG-LP 9/20 MM WS

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Dimensions and weights

| | | | |
|---|---|---|---|
| Depth | 0.05 mm | Depth (inches) | 0.002 inch |
| Height | 9 mm | Height (inches) | 0.3543 inch |
| Width | 20 mm | Width (inches) | 0.7874 inch |
| Net weight | 0.01 g | | |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

### General data

| | | | |
|---|---|---|---|
| Adhesive | Acrylate adhesive | Version | Self-adhesive, halogen-free |
| Width | 20 mm | UL 94 flammability rating | V-0 |
| Operating temperature range, max. | 150 °C | Operating temperature range, min. | -40 °C |
| Colour | white | Halogen | No |
| Basic material | Polyamide | Printed characters | without |
| Approval acc. to UL 969 | Yes | | |

### Device markers

| | |
|---|---|
| Halogen | No |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |

# ESG-LP 9/20 MM WS

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Drawings

