

## MF 5/3.5 MM WS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



### MultiMark MultiFit

For connectors from competitors.

The elastic surface finish makes for simple installation.

This special material enables the strips to be stretched to accommodate slight variations in spacing, especially with long terminal blocks.

A print resolution of 300 dpi also produces a very legible script. Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence
- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence
- ] • Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

### General ordering data

|            |   |
|------------|---|
| Version    | Terminal marker, 5 x 3.5 mm, Pitch in mm (P):<br>3.50 white |
| Order No.  | <a href="#">2885900000</a>                                  |
| Type       | MF 5/3.5 MM WS  |
| GTIN (EAN) | 4064675854500   |
| Qty.       | 1750 items  |

## MF 5/3.5 MM WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 0.7 mm | Depth (inches)  | 0.0276 inch |
| Height     | 5 mm   | Height (inches) | 0.1968 inch |
| Width      | 3.5 mm | Width (inches)  | 0.1378 inch |
| Net weight | 0.04 g |                 |             |

### Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -50...90 °C |
|-----------------------------|-------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### General data

|                                   |              |                                   |         |
|-----------------------------------|--------------|-----------------------------------|---------|
| Version                           | halogen-free | Width                             | 3.5 mm  |
| UL 94 flammability rating         | V-2          | Operating temperature range, max. | 90 °C   |
| Operating temperature range, min. | -50 °C       | Colour                            | white   |
| Basic material                    | PC-ABS, TPU  | Printed characters                | neutral |
| Operating temperature range       | -50...90 °C  |                                   |         |

### Connector markers

|                 |         |
|-----------------|---------|
| Pitch in mm (P) | 3.50 mm |
|-----------------|---------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000761    | ETIM 9.0    | EC000761    |
| ETIM 10.0   | EC000761    | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 |             |             |

Drawings

