


WEP 2C 4 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

| | |
|------------|--|
| Version | End plate for terminals, black, Height: 60 mm, Width: 2 mm, V-0, Wemid, Snap-on: Yes |
| Order No. | 2894230000 |
| Type | WEP 2C 4 BK |
| GTIN (EAN) | 4064675885214 |
| Qty. | 20 items |

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 39 mm | Depth (inches) | 1.5354 inch |
| Height | 60 mm | Height (inches) | 2.3622 inch |
| Width | 2 mm | Width (inches) | 0.0787 inch |
| Net weight | 2.31 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Ambient temperature | -60 °C...85 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C | | |

Environmental Product Compliance

| | | | |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status | Compliant without exemption | | |
| REACH SVHC | No SVHC above 0.1 wt% | | |
| Product Carbon Footprint | Cradle to gate | 0.027 kg CO2 eq. | |

Material data

| | | | |
|---------------------------|-------|--------|-------|
| Basic material | Wemid | Colour | black |
| UL 94 flammability rating | V-0 | | |

Additional technical data

| | |
|---------|-----|
| Snap-on | Yes |
|---------|-----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000886 | ETIM 9.0 | EC000886 |
| ETIM 10.0 | EC000886 | ECLASS 14.0 | 27-25-03-01 |
| ECLASS 15.0 | 27-25-03-01 | | |

MultiFit**MultiMark MultiFit**

For connectors from competitors.

The elastic surface finish makes for simple installation. This special material enables the strips to be stretched to accommodate slight variations in spacing, especially with long terminal blocks.

A print resolution of 300 dpi also produces a very legible script. Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

General ordering data

| | | | |
|------------|----------------------------|-------------------------------------|--|
| Type | EL KSM 10.6 MM WS 30M | Version | |
| Order No. | 2799270000 | Terminal marker, 10.6 x 5 mm, white | |
| GTIN (EAN) | 4064675261032 | | |
| Qty. | 1 ST | | |