

**FUSEHOLDER WSFH/2 10X38 1KV LED**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Photovoltaic fuse holder for PV applications

- For usage in photovoltaic DC combiner boxes up to 1000V
- DIN- rail mounted
- For use with cylindrical fuse links from 1A up to 30A of 10x38mm gPV

**General ordering data**

Version	Photovoltaics, Fuse holder, 1000 V, 10x38, 2 Strings, with LED
Order No.	<a href="#">2896950000</a>
Type	FUSEHOLDER WSFH/2 10X38 1KV LED
GTIN (EAN)	4064675899679
Qty.	5 items

## FUSEHOLDER WSFH/2 10X38 1KV LED

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	61 mm	Depth (inches)	2.4016 inch
Height	73 mm	Height (inches)	2.874 inch
Width	18 mm	Width (inches)	0.7087 inch
Net weight	15.4 g		

### Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	90 °C
----------------------------------	--------	----------------------------------	-------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Fuse holder connection

Number of connections	2	Stripping length	10 mm
Tightening torque, max.	2.5 Nm	Tightening torque, min.	2 Nm
Type of connection	Screw connection	Wire material	Copper
Wire connection cross section AWG, min.	AWG 6	Wire connection cross section AWG, max.	AWG 17
Wire connection cross section, finely stranded, min.	1 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	10 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	1 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	10 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	1 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	10 mm <sup>2</sup>
Wire connection cross-section, solid core, min.	1 mm <sup>2</sup>	Wire connection cross-section, solid core, max.	10 mm <sup>2</sup>

### Fuse holder technical data

Cartridge fuse	10 x 38 mm	Colour	Light Blue
Display	Red LED	Fuse holder (cartridge holder)	Pivoting
Max. current	30 A	Number of potentials	1
Operating voltage, max.	1000 V	Power dissipation, max.	3 W
Mounting rail	TS 35	Rated impulse withstand voltage	6 kV
Surge voltage category	III	Type of mounting	Rail

### Classifications

ETIM 8.0	EC000899	ETIM 9.0	EC000899
ETIM 10.0	EC000899	ECLASS 14.0	27-25-01-13
ECLASS 15.0	27-25-01-13		

FUSEHOLDER WSFH/2 10X38 1KV LED

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Drawings

[www.weidmueller.com](http://www.weidmueller.com)



## FUSEHOLDER WSFH/2 10X38 1KV LED

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

### 10x38 gPV



The gPV cylindrical fuse cartridges are designed to provide compact, safe and economical protection of photovoltaic modules (field protection) with voltages up to 1,500 DC. They provide protection against both overload and short circuit (gPV class according to the requirements of IEC60269-6 and UL248-19 standards). Made of a ceramic tube with high internal pressure and thermal shock resistance, allowing high switching capacity in a small space. The contacts are made of silver-plated copper and the fusible elements of pure silver to avoid ageing and thus keep the electrical characteristics invariable. They are available in the sizes 10x38 mm, 10x85 mm and 22x58 mm.

### General ordering data

Type	FUSE 10X38 1A 1000 VDC ...	Version
Order No.	<a href="#">2783160000</a>	Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 1 A
GTIN (EAN)	4064675059684	
Qty.	10 ST	
Type	FUSE 10X38 2A 1000 VDC ...	Version
Order No.	<a href="#">2783170000</a>	Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 2 A
GTIN (EAN)	4064675059691	
Qty.	10 ST	
Type	FUSE 10X38 3A 1000 VDC ...	Version
Order No.	<a href="#">2783180000</a>	Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 3 A
GTIN (EAN)	4064675059905	
Qty.	10 ST	
Type	FUSE 10X38 4A 1000 VDC ...	Version
Order No.	<a href="#">2783190000</a>	Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 4 A
GTIN (EAN)	4064675059912	
Qty.	10 ST	
Type	FUSE 10X38 5A 1000 VDC ...	Version
Order No.	<a href="#">2783200000</a>	Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 5 A
GTIN (EAN)	4064675059929	
Qty.	10 ST	
Type	FUSE 10X38 6A 1000 VDC ...	Version
Order No.	<a href="#">2783210000</a>	Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 6 A
GTIN (EAN)	4064675059936	
Qty.	10 ST	
Type	FUSE 10X38 8A 1000 VDC ...	Version
Order No.	<a href="#">2783220000</a>	Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 8 A
GTIN (EAN)	4064675059943	
Qty.	10 ST	
Type	FUSE 10X38 10A 1000 VDC...	Version
Order No.	<a href="#">2783230000</a>	Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 10 A
GTIN (EAN)	4064675059950	
Qty.	10 ST	
Type	FUSE 10X38 12A 1000 VDC...	Version
Order No.	<a href="#">2783240000</a>	Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 12 A
GTIN (EAN)	4064675059967	
Qty.	10 ST	

## FUSEHOLDER WSFH/2 10X38 1KV LED

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Accessories

Type	FUSE 10X38 15A 1000 VDC...	Version
Order No.	<a href="#">2783250000</a>	Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 15 A
GTIN (EAN)	4064675059974	
Qty.	10 ST	
Type	FUSE 10X38 16A 1000 VDC...	Version
Order No.	<a href="#">2783260000</a>	Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 16 A
GTIN (EAN)	4064675059981	
Qty.	10 ST	
Type	FUSE 10X38 20A 1000 VDC...	Version
Order No.	<a href="#">2783280000</a>	Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 20 A
GTIN (EAN)	4064675060000	
Qty.	10 ST	
Type	FUSE 10X38 25A 1000 VDC...	Version
Order No.	<a href="#">2827990000</a>	Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 25 A
GTIN (EAN)	4064675367819	
Qty.	10 ST	
Type	FUSE 10X38 30A 1000 VDC...	Version
Order No.	<a href="#">2828000000</a>	Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 30 A
GTIN (EAN)	4064675367826	
Qty.	10 ST	