

WIL-SXXXX-FXSF-5700-X840-M8DX-S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The S-series, available as compact standard and premium lights. The simple M8 connection technology enables plug-and-play as well as the ability for multiple luminaires to be mounted in a row. The light colors of 5.700K or 6.500K can also be smoothly dimmed. Thanks to full encapsulation of the premium variant, the S series offers a high level of tightness and additional protection against ingress of solid foreign bodies $\geq 1.0\text{mm}$ (IP69). In addition to their flat installation height of 18mm, this enables their use in machine interiors.

General ordering data

Order No.	2899980000
Type	WIL-SXXXX-FXSF-5700-X840-M8DX-S
GTIN (EAN)	4064675907039
Qty.	1 items

WIL-SXXXX-FXSF-5700-X840-M8DX-S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data
Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E354496

Dimensions and weights

Depth	30 mm	Depth (inches)	1.1811 inch
Height	17.5 mm	Height (inches)	0.689 inch
Width	840 mm	Width (inches)	33.0708 inch
Net weight	639 g		

Temperatures

Operating temperature -20 - 70°C

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1

SCIP 37ebc061-1fa2-4387-80af-82299a5c3412

Cable technical specifications

Housing main material hard anodised aluminium

Connection data

LED Modul is attachable	yes	Version	pin, straight - socket, straight
Number of poles	4	Coding	A-coded
Connection thread	M8 / M8	Tightening torque	0.6 Nm
Wiring	Pin 1: control white LED 24V DC, Pin 2: NC, Pin 3: GND(-), Pin 4: NC		

Electric data

Rated voltage	24 V DC	Rated current	845.8 mA
Power	20.3 W	Dimmable	yes, stepless dimming

General technical data

Type of connection	Pin connector, Socket connector	Electronic equipment on rolling stock	No
Shape of the LED module	Round	Light colour (CCT)	5700K, White
Light current	2532 lm	Emitting angle	100 °
Illumination level	819 lux	Operating life	60.000 h
Type of mounting	Screw mounting	Drill hole spacing	896 mm
Protection degree	IP40	Efficiency class (according to EU Directive No. 874/2012)	Not required

WIL-SXXXX-FXSF-5700-X840-M8DX-S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Material data**


Material of LED cover	PMMA	Housing main material	hard anodised aluminium
-----------------------	------	-----------------------	-------------------------

Classifications


ETIM 8.0	EC000996	ETIM 9.0	EC000996
ETIM 10.0	EC000996	ECLASS 14.0	27-11-06-35
ECLASS 15.0	27-11-06-35		

Drawings

Dimensioned drawing



Pole scheme



Pole scheme

