
Data sheet

VT-TM 1/30 HF-V0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	, Socket x 5.3 mm, TPU, Colour: yellow, Transparent, Conductor O.D.: 2.5 - 5 mm
Order No.	2902800000
Type	VT-TM 1/30 HF-V0
GTIN (EAN)	4099986005358
Qty.	200 items

Data sheet

VT-TM 1/30 HF-V0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Height	30 mm	Height (inches)	1.1811 inch
Width	5.3 mm	Width (inches)	0.2087 inch
Net weight	0.45 g		

Temperatures

Operating temperature range	-30...90 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of printing	neutral	Width	5.3 mm
UL 94 flammability rating	V-0	Operating temperature range, max.	90 °C
Operating temperature range, min.	-30 °C	Colour	yellow, Transparent
Halogen	No	Basic material	TPU
Printed characters	without	Recommended industries	Transportation, Machinery
Operating temperature range	-30...90 °C		

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	1.5 mm²
Conductor cross-section, min.	0.5 mm²	Conductor O.D., max.	5 mm
Conductor O.D., min.	2.5 mm	Conductor O.D.	2.5 - 5 mm
Cross-section for connected wire	0.5 - 1.5 mm²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		