

IE-FM5Z2LM0010LD0LD0-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Patch cable, duplex clip included, LC-Duplex IP 20, LC-Duplex IP 20, 50 µm, LSZH, 1 m
Order No.	2903650010
Type	IE-FM5Z2LM0010LD0LD0-X
GTIN (EAN)	409998602684 1
Qty.	1 items

IE-FM5Z2LM0010LD0LD0-X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Length	1 m	Length (inches)	39.3701 inch
Net weight	14.96 g		

Temperatures

Storage temperature	Operating temperature	-20 °C...70 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Cable specific standards

Specification for twisted-pair device connection cables	IEC 61156-6, DIN EN 50288-4-2	Specification for checking the symmetrical communication cabling	IEC 61935-3
---	-------------------------------	--	-------------

General standards

Connector standard	IEC 61754-20
--------------------	--------------

Standards

Connector standard	IEC 61754-20
--------------------	--------------

Fibre-optic

Fibre type	GOF, Multimode, OM4	Attenuation	≤ 1.5 dB at 1300 nm, ≤ 3.5 dB at 850 nm
Bandwidth	≥ 500 MHz*km at 1300 nm, ≥ 1500 MHz*km at 850 nm		

Cable structure

Sheath diameter	2 * 1.5 mm	Sheathing colour	Magenta
Standard designations	I-V(ZN)H	Material sheath	LSZH
Cable layout	ZIPCORD	Primary coating	245.00 µm
Core diameter	50 µm		

Mechanical and material properties of cable

Halogen	No	Min. bending radius, repetitive	20 x cable diameter
Min. bending radius, once only	10 x cable diameter	Resistance to spread of flame	IEC 60754-2

Plug

Plug right	LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded	Plug left	LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
------------	--	-----------	--

IE-FM5Z2LM0010LD0LD0-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Plug, left**

Plug left	LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
-----------	--

Plug, right

Plug right	LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
------------	--

Classifications

ETIM 8.0	EC002607	ETIM 9.0	EC002607
ETIM 10.0	EC002607	ECLASS 14.0	27-06-10-03
ECLASS 15.0	27-06-10-03		

Drawings



IE-FM5Z2LM0010LD0LD0-X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

V0 material



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Type	VT SF 5/21 MC NE WS V0	Version
Order No.	1689470001	SlimFix, Conductor and cable markers, 4.8 - 7.4 mm, 21 x 7.4 mm,
GTIN (EAN)	4008190872571	white
Qty.	160 ST	
Type	VT SF 6/21 MC NE WS V0	Version
Order No.	1730560001	SlimFix, Conductor and cable markers, 5.8 - 7.8 mm, 21 x 8.4 mm,
GTIN (EAN)	4008190954611	white
Qty.	160 ST	