

## PZ 2.5 S

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

### General ordering data

Version	0.14mm <sup>2</sup> , 2.5mm <sup>2</sup> , Trapezoidal crimp
Order No.	<a href="#">2903690000</a>
Type	PZ 2.5 S
GTIN (EAN)	4099986027008
Qty.	1 items

## PZ 2.5 S

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	31 mm	Depth (inches)	1.2205 inch
Height	70 mm	Height (inches)	2.7559 inch
Width	160 mm	Width (inches)	6.2992 inch
Length	160 mm	Length (inches)	6.2992 inch
Net weight	290.6 g		

## Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

## Technical data

Version	Mechanical, without interchangeable inserts
---------	---

## Description of contact

Type of contact	Wire-end ferrules with/without plastic collars	Conductor cross-section, max. AWG	AWG 14
Conductor cross-section, min. AWG	AWG 26	Crimping range, max.	2.5 mm <sup>2</sup>
Crimping range, min.	0.14 mm <sup>2</sup>		

## tool data crimping

Wire end ferrules cross-section, max.	2.5 mm <sup>2</sup>	Wire end ferrules cross-section, min.	0.14 mm <sup>2</sup>
Crimping type/profile	Trapezoidal crimp		

## Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		