


## VPU AC II+III 3 R 275/40 S

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Version	Surge voltage arrester, Low voltage, with remote contact, TN-C
Order No.	<a href="#">2907710000</a>
Type	VPU AC II+III 3 R 275/40 S
GTIN (EAN)	4099986182394
Qty.	1 items

**VPU AC II+III 3 R 275/40 S**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Depth	70 mm	Depth (inches)	2.7559 inch
Height	99 mm	Height (inches)	3.8976 inch
Width	36 mm	Width (inches)	1.4173 inch
Net weight	249 g		

**Temperatures**

Storage temperature Operating temperature -40 °C...85 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Connection data, remote alert**

Cross-section for connected wire, solid core, min.	0.2 mm <sup>2</sup>	Stripping length	5 mm
Connection type	Screw connection	Cross-section for connected wire, solid core, max.	1.5 mm <sup>2</sup>
Max. torque	0.4 Nm		

**General data**

Optical function display	green = OK; red = arrester is defective - replace	Segment	Power distribution
Version	with remote contact	Design	Installation housing; 2TE, Insta IP 20
UL 94 flammability rating	V-0	Colour	grey
Protection degree	IP20 in installed state	Mounting rail	TS 35
Operating altitude	≤ 2000 m		

**Insulation coordination acc. to EN 50178**

Surge voltage category III Pollution severity 2

**Rated data IEC / EN**

Number of poles	2	Combined pulse UOC	6 kV
Signalling contact	250 V / 0,5 A	Rated voltage (AC)	230 V
Low voltage network	TN-C	Voltage type	AC
Temporary surge voltage (over-voltage) - TOV	335 V	Fuse protection	No Fuse necessary ≤100 A gG
Response time / fallback time	≤ 25 ns	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Standards	IEC 61643-11, EN 61643-11

**VPU AC II+III 3 R 275/40 S**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

Requirements class, acc. to EN 61643-11	T2, T3	Requirements category acc. to IEC 61643-11	Type II, Type III
Max. continuous voltage, U <sub>c</sub> (AC)	275 V	Discharge current I <sub>n</sub> (8/20µs) wire-PE	20 kA
Discharge current I <sub>max</sub> (8/20µs) wire-PE	40 kA	Protection level U <sub>p</sub> at IN (L/N-PE)	≤ 1.5 kV
Short-circuit current rating ISCCR	25 kA	Discharge current (type III)	3 kA
Integrated back-up fuse	No	Protection level U <sub>p</sub> at IN (L-PE) (type III)	≤ 1 kV

**Connection data**

Conductor connection cross-section PE, stranded, max.	35 mm <sup>2</sup>	Conductor connection cross-section PE, solid, max.	35 mm <sup>2</sup>
Wire connection method	Screw connection	Type of connection	Screw connection
Stripping length, rated connection	15 mm	Tightening torque, max.	1.2 Nm
Wire cross-section, solid, min.	2.5 mm <sup>2</sup>	Wire cross-section, solid, max.	10 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	2.5 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	25 mm <sup>2</sup>
Connection cross-section, stranded, min.	2.5 mm <sup>2</sup>	Connection cross-section, stranded, max.	10 mm <sup>2</sup>

**Electrical data**

Voltage type	AC
--------------	----

**General data**

Number of poles	2	Protection degree	IP20 in installed state
Colour	grey		

**Guarantee**

Time interval	5 years
---------------	---------

**Important note**

Product information	For use in DC applications, please use the fuse of SIBA Type NH2XL aR/aSF DC 1500 V
---------------------	---

**Classifications**


ETIM 8.0	EC000941	ETIM 9.0	EC000941
ETIM 10.0	EC000941	ECLASS 14.0	27-17-12-02
ECLASS 15.0	27-17-12-02		

**VPU AC II+III 3 R 275/40 S**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)



**VPU AC II+III 3 R 275/40 S**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Accessories**

**Crosshead screwdriver Phillips**



VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

**General ordering data**

Type	SDIK PH0 X 60	Version	
Order No.	<a href="#">2749880000</a>	Screwdriver, Blade width (B): 0 mm, 60 mm, Blade thickness (A): 0	
GTIN (EAN)	4050118897081		
Qty.	1 ST		

**Spare arrester**



**General ordering data**

Type	VPU AC II+III 0 L-N 275...	Version	
Order No.	<a href="#">2907800000</a>	Surge voltage arrester, Low voltage, Spare arrester, TN-S, TT	
GTIN (EAN)	4099986189676		
Qty.	1 ST		
Type	VPU AC II+III 0 L3-PEN ...	Version	
Order No.	<a href="#">2907820000</a>	Surge voltage arrester, Low voltage, Spare arrester, TN-S, TT	
GTIN (EAN)	4099986189690		
Qty.	1 ST		