

CRIMPFIX R VARIO PZ3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Version	Automatic machines, Automatic stripper and crimper
Order No.	2912420000
Type	CRIMPFIX R VARIO PZ3
GTIN (EAN)	4099986535992
Qty.	1 items

CRIMPFIX R VARIO PZ3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	485 mm	Depth (inches)	19.0944 inch
Height	565 mm	Height (inches)	22.2441 inch
Width	335 mm	Width (inches)	13.189 inch
Net weight	22000 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cI
REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

PW65 maintenance - automatic stripping/crimping

Drive	Electropneumatic	Wire end ferrules cross-section, max.	2.5 mm ²
Wire end ferrules cross-section, min.	0.5 mm ²	Crimping range, max.	2.5 mm ²
Crimping range, min.	0.5 mm ²	Consumables	Linked wire-end ferrules

Classifications

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		