

URS CA 100 DUO S 6+10 MM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Version	Automatic machines, Replacement part
Order No.	2912450000
Type	URS CA 100 DUO S 6+10 MM
GTIN (EAN)	4099986536029
Qty.	1 items

URS CA 100 DUO S 6+10 MM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	100 mm	Height (inches)	3.937 inch
Net weight	1500 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

PW65 maintenance - automatic stripping/crimping

Wire end ferrules cross-section, max.	10 mm ²	Wire end ferrules cross-section, min.	6 mm ²
Consumables	with plastic collar		

Classifications

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		