

## URS CA 100 DUO S 6+10 MM

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

### General ordering data

Version	Automatic machines, Replacement part
Order No.	<a href="#">2912450000</a>
Type	URS CA 100 DUO S 6+10 MM
GTIN (EAN)	4099986536029
Qty.	1 items

**URS CA 100 DUO S 6+10 MM**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Height	100 mm	Height (inches)	3.937 inch
Net weight	1500 g		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**PW65 maintenance - automatic stripping/crimping**

Wire end ferrules cross-section, max.	10 mm <sup>2</sup>	Wire end ferrules cross-section, min.	6 mm <sup>2</sup>
Consumables	with plastic collar		

**Classifications**

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		