


**THM MT30X 17.5/8 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

**General ordering data**

Version	THM, Device markers, 8 x 17.5 mm, yellow
Order No.	<a href="#">2912630000</a>
Type	THM MT30X 17.5/8 GE
GTIN (EAN)	409998653682 1
Qty.	2500 items

**THM MT30X 17.5/8 GE**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	0.08 mm	Depth (inches)	0.0031 inch
Height	8 mm	Height (inches)	0.315 inch
Width	17.5 mm	Width (inches)	0.689 inch
Net weight	0.04 g		

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Adhesive	Acrylate
Version	Self-adhesive
Width	17.5 mm
UL 94 flammability rating	V-0
Operating temperature range, max.	150 °C
Operating temperature range, min.	-40 °C
Colour	yellow
Halogen	No
Basic material	Polyester
Printed characters	without
Number of markers per packaging unit compatible printer	Form of supply Label reel
Number of markers per combination	1 Label reel = Device markers
Number per roll	2500

**Device markers**

Halogen No

**Classifications**

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		