

H0,34/7

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- For conductors from 0.25 to 6,0 mm² (AWG 24 - 10)
tin-plated copper
dimensional tolerances to DIN 46228 part 1
- supplied loose in polybag

General ordering data

Version	Wire-end ferrule, Standard, 7 mm, 7 mm, No
Order No.	2919630000
Type	H0,34/7
GTIN (EAN)	4099986576759
Qty.	1000 items

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E499744

Dimensions and weights

Height	7 mm	Height (inches)	0.2756 inch
Diameter	1.8 mm	Net weight	0.02 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Version	Standard
---------	----------

Wire-end ferrules

Contact surface diameter (D1)	0.85 mm	Contact surface length (L2)	7 mm
Collar diameter (D2)	1.8 mm	L1 in mm	7.00 mm
Wire connection cross section AWG, max.	AWG 22	Stripping length	7 mm
Conductor cross-section	0.34 mm ²		

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawings

