

**U-OS-CODESYS-BASIC-L**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**



**General ordering data**

Order No.	2924030000
Type	<a href="#">U-OS-CODESYS-BASIC-L</a>
Qty.	1 items

## U-OS-CODESYS-BASIC-L

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Net weight 0 g

### Environmental Product Compliance

RoHS Compliance Status Not affected  
 REACH SVHC No SVHC above 0.1 wt%

### Licence information

Optional additional fieldbus instances, max.	Instances of further fieldbus protocols	CANopen Manager / CANopen Device / PROFIBUS Master / PROFIBUS Slave / Modbus TCP Client / Modbus TCP Server / Modbus RTU Master / Modbus RTU Device
	Number of supported instances, max.	2
Number of supported input/output channels, max.	256	
Generated binary code size, max.	3 MB	
Licence of visualisation software	Name of the included visualisation software licence	CODESYS-VISU-S
	Number of available data points, max.	128 data points
	Name of the additionally bookable visualisation software licence	U-OS-CODESYS-VISU-M
	Number of available data points, max.	2048 data points
	Name of the additionally bookable visualisation software licence	U-OS-CODESYS-VISU-L
	Number of available data points, max.	4096 data points
	Name of the additionally bookable visualisation software licence	U-OS-CODESYS-VISU-XL
	Number of available data points, max.	8192 data points
Licence of communication software	Name of the additionally bookable visualisation software licence	U-OS-CODESYS-VISU-XXL
	Number of available data points, max.	unlimited data points
	Name of the included communication software licence	CODESYS-Communication S
	Number of available data points, max.	512 data points
	Name of the additionally bookable communication software licence	U-OS-CODESYS-Communication M
Selectable ethernet-based fieldbus instances	Number of available data points, max.	4096 data points
	Name of the additionally bookable communication software licence	U-OS-CODESYS-Communication XXL
	Number of available data points, max.	unlimited data points
	Instances of ethernetbased fieldbus protocols	EtherCAT Manager / PROFINET Controller / PROFINET Device / EtherNet/IP Scanner / EtherNet/IP Adapter
	Number of supported instances, max.	0

### System requirements

System requirements for the u-OS App CODESYS Runtime SL	Name of software	CODESYS Development System
	Supported software version	3.5.19.10 or higher
	Licence necessary	No
Runtime version on the device to be licenced	Name of software	CODESYS Control SL Package for Weidmueller u-OS
	Supported software version	4.7.0 or higher
	Licence necessary	No
Runtime version on the device to be licenced	Name of software	u-OS App CODESYS Runtime SL
	Supported software version	4.9.0.0 or higher

**U-OS-CODESYS-BASIC-L**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

| Single device licence necessary | Yes

**Classifications**

ETIM 8.0	EC000809	ETIM 9.0	EC000809
ETIM 10.0	EC000809	ECLASS 14.0	27-24-25-01
ECLASS 15.0	27-24-25-01		