

**U-OS-CODESYS-STANDARD-S**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**



**General ordering data**

Order No.	2924040000
Type	<a href="#">U-OS-CODESYS-STANDARD-S</a>
Qty.	1 items

## U-OS-CODESYS-STANDARD-S

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Net weight	0 g
------------	-----

### Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

### Licence information

Optional additional fieldbus instances, max.	Instances of further fieldbus protocols	CANopen Manager / CANopen Device / PROFIBUS Master / PROFIBUS Slave / Modbus TCP Client / Modbus TCP Server / Modbus RTU Master / Modbus RTU Device
	Number of supported instances, max.	4
Number of supported input/output channels, max.	512	
Generated binary code size, max.	3 MB	
Licence of visualisation software	Name of the included visualisation software licence	CODESYS-VISU-S
	Number of available data points, max.	128 data points
	Name of the additionally bookable visualisation software licence	U-OS-CODESYS-VISU-M
	Number of available data points, max.	2048 data points
	Name of the additionally bookable visualisation software licence	U-OS-CODESYS-VISU-L
	Number of available data points, max.	4096 data points
	Name of the additionally bookable visualisation software licence	U-OS-CODESYS-VISU-XL
	Number of available data points, max.	8192 data points
Licence of communication software	Name of the included communication software licence	CODESYS-Communication S
	Number of available data points, max.	512 data points
	Name of the additionally bookable communication software licence	U-OS-CODESYS-Communication M
	Number of available data points, max.	4096 data points
	Name of the additionally bookable communication software licence	U-OS-CODESYS-Communication XXL
Selectable ethernet-based fieldbus instances	Instances of ethernetbased fieldbus protocols	EtherCAT Manager / PROFINET Controller / PROFINET Device / EtherNet/IP Scanner / EtherNet/IP Adapter
	Number of supported instances, max.	1

### System requirements

System requirements for the u-OS App CODESYS Runtime SL	Name of software	CODESYS Development System
	Supported software version	3.5.19.10 or higher
	Licence necessary	No
	Name of software	CODESYS Control SL Package for Weidmueller u-OS
	Supported software version	4.7.0 or higher
Runtime version on the device to be licenced	Name of software	u-OS App CODESYS Runtime SL
	Supported software version	4.9.0.0 or higher

**U-OS-CODESYS-STANDARD-S**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

| Single device licence necessary | Yes

**Classifications**

ETIM 8.0	EC000809	ETIM 9.0	EC000809
ETIM 10.0	EC000809	ECLASS 14.0	27-24-25-01
ECLASS 15.0	27-24-25-01		