

U-OS-CODESYS-PERFORMANCE-L

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



General ordering data

| | |
|-----------|--|
| Order No. | 2924080000 |
| Type | U-OS-CODESYS-PERFORMANCE-L |
| Qty. | 1 items |

U-OS-CODESYS-PERFORMANCE-L

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | |
|------------|-----|
| Net weight | 0 g |
|------------|-----|

Environmental Product Compliance

| | |
|------------------------|-----------------------|
| RoHS Compliance Status | Not affected |
| REACH SVHC | No SVHC above 0.1 wt% |

Licence information

| | | |
|---|--|---|
| Optional additional fieldbus instances, max. | Instances of further fieldbus protocols | CANopen Manager / CANopen Device / PROFIBUS Master / PROFIBUS Slave / Modbus TCP Client / Modbus TCP Server / Modbus RTU Master / Modbus RTU Device |
| | Number of supported instances, max. | 16 |
| Number of supported input/output channels, max. | 16384 | |
| Generated binary code size, max. | 18 MB | |
| Licence of visualisation software | Name of the included visualisation software licence | CODESYS-VISU-S |
| | Number of available data points, max. | 128 data points |
| | Name of the additionally bookable visualisation software licence | U-OS-CODESYS-VISU-M |
| | Number of available data points, max. | 2048 data points |
| | Name of the additionally bookable visualisation software licence | U-OS-CODESYS-VISU-L |
| | Number of available data points, max. | 4096 data points |
| | Name of the additionally bookable visualisation software licence | U-OS-CODESYS-VISU-XL |
| | Number of available data points, max. | 8192 data points |
| Licence of communication software | Name of the additionally bookable visualisation software licence | U-OS-CODESYS-VISU-XXL |
| | Number of available data points, max. | unlimited data points |
| | Name of the included communication software licence | CODESYS-Communication S |
| | Number of available data points, max. | 512 data points |
| | Name of the additionally bookable communication software licence | U-OS-CODESYS-Communication M |
| Selectable ethernet-based fieldbus instances | Number of available data points, max. | 4096 data points |
| | Name of the additionally bookable communication software licence | U-OS-CODESYS-Communication XXL |
| | Number of available data points, max. | unlimited data points |
| | Instances of ethernetbased fieldbus protocols | EtherCAT Manager / PROFINET Controller / PROFINET Device / EtherNet/IP Scanner / EtherNet/IP Adapter |
| | Number of supported instances, max. | 8 |

System requirements

| | | |
|---|----------------------------|---|
| System requirements for the u-OS App CODESYS Runtime SL | Name of software | CODESYS Development System |
| | Supported software version | 3.5.19.10 or higher |
| | Licence necessary | No |
| | Name of software | CODESYS Control SL Package for Weidmueller u-OS |
| | Supported software version | 4.7.0 or higher |
| Runtime version on the device to be licenced | Licence necessary | No |
| | Name of software | u-OS App CODESYS Runtime SL |
| | Supported software version | 4.9.0.0 or higher |

U-OS-CODESYS-PERFORMANCE-L

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

| Single device licence necessary | Yes

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000809 | ETIM 9.0 | EC000809 |
| ETIM 10.0 | EC000809 | ECLASS 14.0 | 27-24-25-01 |
| ECLASS 15.0 | 27-24-25-01 | | |