

THM WO-R VIN 12.7/19.1 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

**General ordering data**

Version	Conductor and cable markers, 12.7 x 19.1 mm, white
Order No.	2932070000
Type	THM WO-R VIN 12.7/19.1 WS
GTIN (EAN)	4099986670792
Qty.	7450 items

THM WO-R VIN 12.7/19.1 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.07 mm	Depth (inches)	0.0028 inch
Height	12.7 mm	Height (inches)	0.5 inch
Width	19.1 mm	Width (inches)	0.752 inch
Net weight	0.07 g		

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Type of printing	neutral	Width	19.1 mm
UL 94 flammability rating	V-0	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C	Colour	white
Halogen	Yes	Basic material	Vinyl film
Printed characters	without	Number per roll	7450

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	12 mm ²
Conductor O.D., max.	4 mm	Conductor O.D., min.	2 mm
Cross-section for connected wire	12 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

THM WO-R VIN 12.7/19.1 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 76/360 SW	Version	
Order No.	2005080000	Ink ribbon	
GTIN (EAN)	4050118389951		
Qty.	1 ST		