

## THM WO-R VIN 12.7/38.1 WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Version	Conductor and cable markers, 12.7 x 38.1 mm, white
Order No.	<a href="#">2932 100000</a>
Type	THM WO-R VIN 12.7/38.1 WS
GTIN (EAN)	4099986670822
Qty.	4000 items

**THM WO-R VIN 12.7/38.1 WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	0.07 mm	Depth (inches)	0.0028 inch
Height	12.7 mm	Height (inches)	0.5 inch
Width	38.1 mm	Width (inches)	1.5 inch
Net weight	0.14 g		

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Type of printing	neutral	Width	38.1 mm
UL 94 flammability rating	V-0	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C	Colour	white
Halogen	Yes	Basic material	Vinyl film
Printed characters	without	Number per roll	7450

**Conductor and cable markers**

Halogen	Yes	Conductor cross-section, max.	50 mm <sup>2</sup>
Conductor O.D., max.	8 mm	Conductor O.D., min.	4 mm
Cross-section for connected wire	50 mm <sup>2</sup>		

**Classifications**

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

## THM WO-R VIN 12.7/38.1 WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Accessories

## Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

## General ordering data

Type	RIBBON MM 76/360 SW	Version	
Order No.	<a href="#">2005080000</a>	Ink ribbon	
GTIN (EAN)	4050118389951		
Qty.	1 ST		