

KLIPPON K75 RAL7001

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The aluminium Klippon® K enclosures are suitable for use in an extremely wide range of different areas. Various components can be installed inside the enclosures, and will benefit in particular from the high temperature resistance, the excellent IP protection and the good impact resistance.

No matter what kind of application the customer is planning, Weidmüller is able to provide a wide range of aluminium enclosures precisely fitting the customer's requirements.

Klippon® K enclosures for hazardous areas are available on request.

Our extensive product range offers the following advantages:

- Available in two surface finishes: natural and powder-coated (RAL 7001)
 - With chloroprene moulded seal as standard (silicone moulded seal optionally available)
 - Standardised closure system with Torx slotted screw head for 19 enclosure sizes
 - Mounting holes outside of the gasket area
 - High IP protection classes: IP66, IP67 and IP68 according to DIN EN 60529
 - Impact resistance of up to 7 (10) Joules
 - The enclosures are approved according to ATEX, IECEx, cULus, and DNV GL as well as the empty enclosure standard.
- Suitable for railway applications according to EN 45545-2:2013
 - Alloy is resistant to salt water
 - Standardised distributor enclosures with threaded holes and a variety of terminal configurations

General ordering data

Version	Klippon K (aluminium empty enclosure), Empty enclosure, Aluminium enclosure, Height: 230 mm, Width: 330 mm, Depth: 181 mm, Basic material: Aluminium AlSi12, Powder-coated, Silver grey
Order No.	2934170000
Type	KLIPPON K75 RAL7001
GTIN (EAN)	4099986682405
Qty.	1 items

KLIPPON K75 RAL7001

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	181 mm	Depth (inches)	7.126 inch
Height	230 mm	Height (inches)	9.0551 inch
Width	330 mm	Width (inches)	12.9921 inch
Mounting dimension - height	210 mm	Mounting dimension - width	310 mm
Wall thickness, min.	5 mm	Wall thickness, max.	5 mm
Net weight	5160 g		

Temperatures

Operating temperature	-40 °C...80 °C
-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Cable glands, right

M25	9	M63	1
M75	1	M16	16
M40	4	M50	2
M32	4	M20	16
M12	36		

Cable glands, top/bottom

M20	32	M12	72
M63	2	M40	8
M32	10	M25	18
M50	4	M75	1
M16	36		

Certificate numbers enclosure

Declaration of Conformity No. (DoC LVD)	DE PS2410 160412 001ISS03	Approval conditions	cULus
---	------------------------------	---------------------	-------

General information

Material thickness of cover	5 mm	Material thickness of enclosure	5 mm
Material thickness	5 mm	Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C	Lid attachment	M6 torx stainless steel screws with slot
Installation advice	Wall mounting	Standards	DIN EN 45545-2
Surface finish	Powder-coated	Impact resistance	10 J version standard
Protection degree	IP66, IP67, IP68	Basic material	Aluminium AlSi12
Seal material	Chloroprene	Torque for lid screws	2.5 Nm
Protection class (UL)	Type 4, Type 4X	Number of lid screws	4
Access opening: width	300 mm	Flange plate	No
Lid	Yes	Access opening: height	220 mm

KLIPPON K75 RAL7001

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Areas of use	Process industry, Transportation, Marine engineering, Packaging industry, Harbour facilities, Machine construction
--------------	--

horizontal assembly

WDU 10 / ZDU 10	2x28	WDU 16 / ZDU 16	2x24
WDU 2,5 / ZDU 2,5 / IDU 2,5	2x55	WDU 35 / ZDU 35	2x17
WDU 4 / ZDU 4	2x46	WDU 6 / ZDU 6	2x35

vertical assembly

WDU 10 / ZDU 10	2x17	WDU 16 / ZDU 16	2x15
WDU 2,5 / ZDU 2,5 / IDU 2,5	2x34	WDU 35 / ZDU 35	2x11
WDU 4 / ZDU 4	2x29	WDU 6 / ZDU 6	2x22

Classifications

ETIM 8.0	EC000261	ETIM 9.0	EC000261
ETIM 10.0	EC000261	ECLASS 14.0	27-18-01-01
ECLASS 15.0	27-18-01-01		

KLIPPON K75 RAL7001

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Klippon® K - Hinge



The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS 15
- Mounting plates
- Hinges
- Wall-mounted holder

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

Type	HG K+POK	Version	
Order No.	1580360000	Klippon POK (polyester empty enclosure), External joint, Hinge, Basic	
GTIN (EAN)	4008190203542	material: Aluminium AISi12, silver	
Qty.	1 ST		

Spacer



Stainless steel spacers in three lengths to increase the distance between the mounting rails or DIN rails and the rear wall of the enclosure.

General ordering data

Type	SP M6 15 MSZN	Version	
Order No.	3896100000	Klippon EB (Essential Box), Spacer, Height: 11.2 mm, Width: 10 mm,	
GTIN (EAN)	4008190857851	Depth: 15 mm, Basic material: Steel, silver	
Qty.	2 ST		
Type	SP M6 20 MSZN	Version	
Order No.	3896200000	Klippon EB (Essential Box), Spacer, Height: 11.2 mm, Width: 10 mm,	
GTIN (EAN)	4008190850234	Depth: 20 mm, Basic material: Steel, silver	
Qty.	2 ST		
Type	SP M6 30 MSZN	Version	
Order No.	3896300000	Klippon EB (Essential Box), Spacer, Height: 11.2 mm, Width: 10 mm,	
GTIN (EAN)	4008190850241	Depth: 30 mm, Basic material: Steel, silver	
Qty.	2 ST		

KLIPPON K75 RAL7001

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Klippon® K - Wall-mounted holder



The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS 15
- Mounting plates
- Hinges
- Wall-mounted holder

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

Type	KLIPPON K MF KIT 25	Version	
Order No.	9527590000	Klippon K (aluminium empty enclosure), Mounting foot, Fixing lugs,	
GTIN (EAN)	4032248014071	Height: 70 mm, Width: 33.5 mm, Depth: 12 mm, Basic material:	
Qty.	1 ST	Stainless steel 1.4301, silver	

Mounting support



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Type	FKSC M5X8 D9/SW2.5	Version	
Order No.	0295900000	SAK Series, Allen hex screw, Screws, Number of poles: 1	
GTIN (EAN)	4008190133337		
Qty.	50 ST		

Depth 15 mm



The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS 15
- Mounting plates
- Hinges
- Wall-mounted holder

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

Type	TS35X15 ST 202 K75 VER	Version	
Order No.	8000135666	Rail, TS 35 x 15, Width: 202 mm, without slot, with slot, Steel,	
GTIN (EAN)	4099987090049	galvanic zinc plated and passivated	
Qty.	1 ST		

KLIPPON K75 RAL7001

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	TS35X15 ST 306 K75 HOR	Version
Order No.	8000135664	Rail, TS 35 x 15, Width: 306 mm, without slot, with slot, Steel,
GTIN (EAN)	4099987089920	galvanic zinc plated and passivated
Qty.	1 ST	

Depth 7.5 mm



The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS 15
- Mounting plates
- Hinges
- Wall-mounted holder

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

Type	TS35X7.5 ST 202 K75 VER	Version
Order No.	8000135665	Rail, Width: 202 mm, without slot, with slot, Steel, galvanic zinc
GTIN (EAN)	4099987090032	plated and passivated
Qty.	1 ST	
Type	TS35X7.5 ST 306 K75 HOR	Version
Order No.	8000135663	Rail, TS 35 x 7.5, Width: 306 mm, with slot, Steel, galvanic zinc
GTIN (EAN)	4099987090001	plated and passivated
Qty.	1 ST	