

PROTECTIVE COVER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Devices in this series display universal analogue process values.

Depending on the version, the devices convert/isolate the signals into an analogue current signal and have additional limit value relays which switch further signals.

Features:

- Several sensor variants can be processed.
- An auxiliary power supply is required.
- Even in unfavourable lighting conditions, the display value is clearly visible.

General ordering data

Version	Display, Hood, Input : I/U universal, 0-20 mA, HART® transparent, Output : Potentiometer, Temperature, thermocouple
Order No.	2964330000
Type	PROTECTIVE COVER
GTIN (EAN)	4099986768086
Qty.	1 items

PROTECTIVE COVER

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	120 mm	Depth (inches)	4.7244 inch
Height	48.8 mm	Height (inches)	1.9213 inch
Width	96.6 mm	Width (inches)	3.8031 inch
Net weight	36.96 g		

Temperatures

Storage temperature Operating temperature

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Type of mounting Front mounting Protection degree IP65

Input

Type other

Insulation coordination

Galvanic isolation Without isolation

Classifications

ETIM 8.0	EC000677	ETIM 9.0	EC000677
ETIM 10.0	EC000677	ECLASS 14.0	27-14-31-10
ECLASS 15.0	27-14-31-10		

PROTECTIVE COVER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Example of use

