

**WIL-AXXXX-FXSF-5700-X800-GST**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



**General ordering data**

Order No.	2979350000
Type	<a href="#">WIL-AXXXX-FXSF-5700-X800-GST</a>
GTIN (EAN)	4099986832794
Qty.	1 items

## WIL-AXXXX-FXSF-5700-X800-GST

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	135 mm	Depth (inches)	5.3149 inch
Height	38 mm	Height (inches)	1.4961 inch
Width	816 mm	Width (inches)	32.1259 inch
Net weight	300 g		

### Temperatures

Operating temperature	-20 - 45°C
-----------------------	------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	60b0f8b3-d5d4-4f2d-a3c8-d2f055e5e550

### Cable technical specifications

Housing main material	hard anodised aluminium
-----------------------	-------------------------

### Connection data

Number of poles	3
-----------------	---

### Electric data

Rated voltage	230 V AC	Power	32.5 W
Dimmable	yes, stepless dimming		

### General technical data

Light colour (CCT)	5700K, White	Light current	5825 lm
Emitting angle	100 °	Operating life	60.000 h
Type of mounting	Screw mounting	Protection degree	IP40

### Material data

Housing main material	hard anodised aluminium
-----------------------	-------------------------

### Classifications

ETIM 8.0	EC000996	ETIM 9.0	EC000996
ETIM 10.0	EC000996	ECLASS 14.0	27-11-06-35
ECLASS 15.0	27-11-06-35		